



## Conductivity/Resistivity Indicators with Analog and Digital Displays



CDCN-5800  
**\$917**



Consult Omega's Flow Engineering Department for mounting accessories.

CDCN-5800, \$917, shown larger than actual size.

CDCE-90-1, \$298, shown larger than actual size. See page E-37.

- ✓ Simple Pushbutton Operation
- ✓ Wide Range of Operation
- ✓ Programmable Temperature Compensation and TDS Conversion Factors
- ✓ 12 to 24 Vdc/Vac Powered

The CDCN-5800 conductivity/resistivity indicator can accommodate a complete range of applications without factory configuration. Software menu control of temperature compensation, plus options to display  $\mu\text{S}$ ,  $\text{mS}$ ,  $\text{K}\Omega$ ,  $\text{M}\Omega$  or PPM (TDS) provide a wide dynamic range of operation. Linearity is assured over a wide range without the need for troublesome platinized or graphite electrodes, thanks to state-of-the-art electronics.

### Specifications

**Compatible Sensors:** CDCE-90-X Series (see page E-38)  
**Accuracy:**  $\pm 2\%$  of reading

**Input Range:** 0.055 to 400,000  $\mu\text{S}$  (10  $\text{K}\Omega$  to 18.3  $\text{M}\Omega$ )

**Temp Comp PT1000:** 0 to 100°C (32 to 212°F), optically isolated

**Display:**

**Update Rate:** <2 sec.

**Displayed Units:**  $\mu\text{S}$ ,  $\text{mS}$ ,  $\text{K}\Omega$ ,  $\text{M}\Omega$ , PPM (TDS)

**Relay Outputs:** Mechanical SPDT Contacts contact rating 5 A @ 30 Vdc, 5 A @ 125 Vac, 3 A @ 250 Vac

**Hysteresis:** User adjustable

**Current Output Range:** 4 to 20 mA with adjustable span

**Accuracy:**  $\pm 0.1\%$

**Dimensions:** 97 L x 97 W x 76 mm D (3.8 x 3.8 x 3.0")

**AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model Number)

Model No.	Price	Description
CDCN-5800	\$917	Conductivity/resistivity indicator, including reversible dial face kit (0-2, 4, 6, 8, 10, 100) and assorted conductivity unit/multiplier decals

Comes complete with operator's manual. Order electrode separately (see pages E-37 to E-38).

**Ordering Example:** CDCN-5800 conductivity/resistivity indicator with analog and digital displays, \$917.

Recommended Reference Book: Calibration, A Technician's Guide 2005, OP-20, \$79. See Section Y for Additional Books



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters