

ECONOMICAL DRUM PUMPS

FPUD150 Series
Starts at
\$202



- ✓ Very Economical
- ✓ Corrosion-Resistant Polypropylene Tube
- ✓ Portable and Lightweight
- ✓ Intermittent Duty
- ✓ Rugged Construction for Industrial Use
- ✓ Push-Button Operation
- ✓ Splashproof Motor

The FPUD150 Series drum pump is both labor and cost efficient. It is the best value drum pump on the market. Designed to replace hand pumps or awkward air-operated diaphragm pumps, it is extremely lightweight and easy to handle. The combination of corrosion-resistant polypropylene tubing and its electric motor makes it a perfect choice for intermittent duty chemical transfer applications.

SPECIFICATIONS

Maximum Fluid Specific Gravity: 1.4
Maximum Temperature: 49°C (120°F)
 23 l/min (6 gpm) maximum flow rate
Maximum Viscosity: 150 centistokes
Maximum Head: 3 m (10')



FPUD151, pump motor, \$218, with FPUD1-P27, insertion tube, \$148, shown smaller than actual size.

Tubes (1 Tube required)

AVAILABLE FOR FAST DELIVERY!

Model No.	Price	Material	Tube Diameter mm (in)	Length mm (in)	Seal	Shaft	Internals	Hose Size mm (in)	Weight kg (lb)
FPUD1-P27	\$148	Polypropylene	25 (1)	685 (27)	Graphite-filled PTFE	316 SS	Polypropylene, PTFE, PVDF, FKM	19 (¾)	0.9 (2)
FPUD1-P40	186		25 (1)	1016 (40)					1.4 (3)

Motors

Model No.	Price	Type	Certifications	Electrical Requirements	Output	RPM	Wt kg (lb)
FPUD151	\$218	IP44 enclosure	CE	220 to 240 Vac/50 to 60 Hz	100 W	10,000	1.4 (3)
FPUD152	202	Splashproof enclosure	—	120 Vac/50 to 60 Hz	½ HP	10,000	1.4 (3)

Accessory

Model No.	Price	Description
OP-17	\$15	Reference Book: Measure for Measure

Comes complete with operator's manual. Motors also supplied with power cord.

Ordering Example: FPUD151 drum pump with CE certification, FPUD1-P40, 40" tube, \$218 + 186 = \$404.



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters