

Mini Vacuum Desiccator *Ideal for Small Samples*

LAB-410990000

- Interior Volume: 0.015 Cu. Ft.
- Vacuum Rating of 740 mm Hg (29")
- Clear Polycarbonate Top; White Polypropylene Bottom
- Stopcock with 2 mm (0.08") PTFE Plug
Uses 6 mm (¼") Tubing
- Peripheral Flange Around the Bottom Fits Into Two Snap
Locks and Seals the Two Halves Against a Buna-O-Ring



LAB-410990000 shown smaller than actual size.

To Order

Model No.	Description	Dimensions (Diameter x H)
LAB-410990000	Mini vacuum desiccator	17.5 x 12.6 cm (6¾ x 5")