

IMMERSION HEATERS

OVER-THE SIDE IMMERSION HEATERS FOR MILDLY CORROSIVE FLUIDS

TLS and KTLS Series
Starts at

\$1007

- ✓ 2 to 18 kW
- ✓ 120, 240, 480V, 1 and 3 Phase
- ✓ Stainless Steel Sheath and Riser Elements
- ✓ Optional Thermostat Kits are Available to Fit into Terminal Box

FEATURES

These over-the-side immersion heaters are designed for installing in the top of a tank with the heated portion directly immersed along the side or at the bottom. This provides easy removal of the heater and ample working space inside the tank.



APPLICATIONS

Alkaline cleaners (electrified), alkaline soaking cleaners, copper sulfate, electroless copper, electro cleaners, mild acid baths, wash tanks dip tanks containing alkali, oakite, caustic soda, detergent and other aqueous solutions

SPECIFICATIONS

Wattage: 2 to 18 kW

Power: 120, 240, 480V, 1 & 3

Watt Density: 40 w/in²

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.



TLS-220A-036/120V, \$1007, shown smaller than actual size.

KTLS-220A-036/120V, \$1104, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

kW	Riser (A) cm (in)	Straight Elements			Curved Elements			Wt. lb (kg)
		Min. Tank Clearance (B)—cm (in)	Model No.	Price	Min. Tank Clearance (B)—cm (in)	Model No.	Price	
Two Elements — Stainless Steel, 40 W/in.²								
2	91 (36)	31 (12¼)	TLS-220A-036/120	\$1007	27 (10½)	KTLS-220A-036/120	\$1104	8 (4)
2	91 (36)	31 (12¼)	TLS-220A-036/*	1007	27 (10½)	KTLS-220A-036/*	1104	8 (4)
4	91 (36)	57 (22¼)	TLS-240A-036/120	1098	35 (13¾)	KTLS-240A-036/120	1206	8 (4)
4	91 (36)	57 (22¼)	TLS-240A-036/*	1098	35 (13¾)	KTLS-240A-036/*	1206	8 (4)
6	91 (36)	75 (29½)	TLS-260A-036/120	1191	41 (16½)	KTLS-260A-036/120	1306	10 (5)
6	91 (36)	75 (29½)	TLS-260A-036/*	1191	41 (16½)	KTLS-260A-036/*	1306	10 (5)
8	91 (36)	95 (37¾)	TLS-280A-036/*	1329	47 (18½)	KTLS-280A-036/*	1353	12 (5)
10	121 (48)	103 (45)	TLS-210A-048/*	1379	54 (21¼)	KTLS-210A-048/*	1442	14 (6)
12	121 (48)	133 (52½)	TLS-212A-048/*	1479	59 (23½)	KTLS-212A-048/*	1531	16 (7)
Three Elements — Stainless Steel, 40 W/in.²								
3	91 (36)	31 (12¼)	TLS-330A-036/120	\$1143	27 (10½)	KTLS-330A-036/120	\$1260	9 (4)
3	91 (36)	31 (12¼)	TLS-330A-036/240/**	1143	27 (10½)	KTLS-330A-036/240/**	1260	9 (4)
3	91 (36)	31 (12¼)	TLS-330A-036/480/**	1143	27 (10½)	KTLS-330A-036/480/**	1260	9 (4)
6	91 (36)	57 (22¼)	TLS-360A-036/120	1270	35 (13¾)	KTLS-360A-036/120	1397	10 (5)
6	91 (36)	57 (22¼)	TLS-360A-036/240/**	1270	35 (13¾)	KTLS-360A-036/240/**	1397	10 (5)
6	91 (36)	57 (22¼)	TLS-360A-036/480/**	1270	35 (13¾)	KTLS-360A-036/480/**	1397	10 (5)
9	91 (36)	75 (29½)	TLS-390A-036/240/**	1338	41 (16½)	KTLS-390A-036/240/**	1469	12 (5)
9	91 (36)	75 (29½)	TLS-390A-036/480/**	1338	41 (16½)	KTLS-390A-036/480/**	1469	12 (5)
12	121 (48)	95 (37¾)	TLS-312A-048/240/**	1440	47 (18½)	KTLS-312A-048/240/**	1582	14 (6)
12	121 (48)	95 (37¾)	TLS-312A-048/480/**	1440	47 (18½)	KTLS-312A-048/480/**	1582	14 (6)
15	121 (48)	103 (45)	TLS-315A-048/240/**	1540	54 (21¼)	KTLS-315A-048/240/**	1692	16 (7)
15	121 (48)	103 (45)	TLS-315A-048/480/**	1540	54 (21¼)	KTLS-315A-048/480/**	1692	16 (7)
18	121 (48)	133 (52½)	TLS-318A-048/240/**	1634	60 (23½)	KTLS-318A-048/240/**	1795	18 (8)
18	121 (48)	133 (52½)	TLS-318A-048/480/**	1634	60 (23½)	KTLS-318A-048/480/**	1795	18 (8)

* Designate voltage, i.e. insert “-240” for 240 for “-480V” for 480 V. ** Add the suffix “3P” to the model number for 3 phase power. Optional thermostat kits are available to fit into heater terminal box.

Ordering Examples: TLS-220A-036/240, 2 kW heater powered by 1 phase 240 Vac, \$1007. TLS-330A-036/240/3P, 3 kW heater powered by 3 phase 240 Vac, \$1143.

To Order, Call **1-800-872-4328** or Shop Online at **omega.comSM**

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters