

ELECTRONIC VACUUM GAUGE

DVG-60
\$135



- ✓ **Pocket Size**
- ✓ **Cleanable Thermistor Sensor for Repeat Accuracy**
- ✓ **Single Switch Operation**
- ✓ **Low-Battery Indication**
- ✓ **Color-Coded LED Display**
- ✓ **Built-In Hanger/Stand Support**
- ✓ **Vinyl Protective Case Included**

The OMEGA DVG-60 is a durable, self-contained, battery-powered electronic vacuum gauge that displays the level of vacuum on an LED color-coded readout.

The 10-segment, color-coded LED readout provides fast response in vacuum measurements. The LEDs indicate vacuum level from 5000 microns down to 50 microns.

SPECIFICATIONS

Range: 10 segments from atmosphere to 50 microns

Power: 9 V alkaline battery (included)

Dimensions: 140 H x 44.5 W x 38 mm D (5.5 x 1.75 x 1.5")

Fitting: 1/4" flair

Case: Polycarbonate

Carrying Case: Included

Weight: 180 g (6.3 oz)



DVG-60, \$135, shown actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

RANGE	MODEL NO.	PRICE
Atmosphere to 50 microns	DVG-60	\$135

Comes with operator's manual and battery.

Ordering Example: DVG-60, digital vacuum gauge, \$135.

Recommended Reference Book: Actuator Saturation Control
CM-4365, \$160. See Section Y for Additional Books



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters