

SUBMINIATURE AND MINIATURE LOAD CELLS IN ECONOMICAL 3-PACKS

Starts at
£555
3-Pack



- ✓ Most Popular Ranges Available for Immediate Delivery
- ✓ Supplied with Certificate of Conformance to Published Specifications
- ✓ Calibrate with Known Weights
- ✓ Sold in Economical 3-Packs
- ✓ Same Rugged Construction and High Accuracy at an Economical Price

LCKD Series
Compression
0-0.4 lb to 0-1000 lb
0-1 kg to 0-455 kg



LCGD Series
Compression
0-25 lb to 0-50,000 lb
0-11 kg to 0-22,686 kg



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

CAPACITY		MODEL NO.	PRICE	COMPATIBLE METERS*
lb	kg			
2.2	1	LCKD-1KG-PK	£705	DPiS, DP41-S, DP25B-S
5	2.3	LCKD-5-PK	665	DPiS, DP41-S, DP25B-S
10	4.5	LCKD-10-PK	665	DPiS, DP41-S, DP25B-S
25	11	LCKD-25-PK	665	DPiS, DP41-S, DP25B-S
50	23	LCKD-50-PK	665	DPiS, DP41-S, DP25B-S
100	45	LCKD-100-PK	665	DPiS, DP41-S, DP25B-S
250	114	LCKD-250-PK	665	DPiS, DP41-S, DP25B-S
500	227	LCKD-500-PK	665	DPiS, DP41-S, DP25B-S
1000	455	LCKD-1000-PK	665	DPiS, DP41-S, DP25B-S

Comes with certificate of conformance.

* See section D for compatible meters.

Ordering Examples: LCKD-1KG-PK, 1 kg capacity load cell, £705. LCKD-25-PK, 25 lb capacity load cell, £995.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

CAPACITY		MODEL NO.	PRICE	COMPATIBLE METERS*
lb	kg			
25	11	LCGD-25-PK	£715	DPiS, DP41-S, DP25B-S
50	23	LCGD-50-PK	715	DPiS, DP41-S, DP25B-S
100	45	LCGD-100-PK	715	DPiS, DP41-S, DP25B-S
250	114	LCGD-250-PK	555	DPiS, DP41-S, DP25B-S
500	227	LCGD-500-PK	555	DPiS, DP41-S, DP25B-S
1000	455	LCGD-1K-PK	555	DPiS, DP41-S, DP25B-S
2000	909	LCGD-2K-PK	555	DPiS, DP41-S, DP25B-S
5000	2269	LCGD-5K-PK	635	DPiS, DP41-S, DP25B-S
10,000	4537	LCGD-10K-PK	635	DPiS, DP41-S, DP25B-S
15,000	6806	LCGD-15K-PK	755	DPiS, DP41-S, DP25B-S
20,000	9074	LCGD-20K-PK	755	DPiS, DP41-S, DP25B-S
30,000	13,612	LCGD-30K-PK	755	DPiS, DP41-S, DP25B-S
50,000	22,686	LCGD-50K-PK	840	DPiS, DP41-S, DP25B-S

Comes with certificate of conformance.

* See section D for compatible meters.

Ordering Examples: LCGD-5K-PK, 5000 lb capacity load cell, £635. LCGD-25-PK, 25 lb capacity load cell, £715.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
OP-17	£10	Reference Book: Measure for Measure



omega.com®

Your One-Stop Source for Process Measurement and Control!

One Omega Drive | Stamford, CT 06907 | 1-888-TC-OMEGA (1-888-826-6342) | info@omega.com

www.omega.com



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488

FRANCE

www.omega.fr

Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl

Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters

• [click here to go to the omega.com home page](http://www.omega.com) •