

HIGHLY ACCURATE, LOW-PRESSURE LABORATORY TRANSMITTER

PX655 Series
 0-0.1 to 0-50 inH₂O
 0-25 Pa to 0-1.25 kPa

Starts at
\$395



PX655-01DI, \$395, with DP3002-E meter, \$285, shown smaller than actual size, see section D.

Ideal Applications:

- ✓ Clean Rooms
- ✓ HVAC
- ✓ Fume Hoods
- ✓ Laboratory Monitoring

SPECIFICATIONS

Excitation: 12 to 36 Vdc
 Output: 4 to 20 mA (2 wire)
 Linearity: 0.3% FS (BFSL)
 Hysteresis: 0.02% FS
 Repeatability: 0.05% FS
 Operating Temp: -29 to 72°C (-20 to 160°F)
 Compensated Temp: 2 to 57°C (35 to 135°F)
 Thermal Effects:
 Zero: 0.015% FS/°F
 Span: 0.015% rdg/°F
 Proof Pressure: 15 psi
 Burst Pressure: 20 psi
 Static Pressure: 25 psi
 Gage Type: Capacitance
 Max Loop Resistance:
 (Supply voltage – 12) x 50 Ω
 Calibration Report: NIST cal at 25, 50, 75 and 100% FS; upscale and downscale provided
 Response Time: 250 ms
 Wetted Parts: Dry, clean, non-corrosive gases only
 Enclosure: NEMA 2 (IP62), 107 H x 117 W x 53 mm D (4.2 x 4.6 x 2.1")
 Pressure Port: 1/8" barbed fittings (tubing TY-316-100)
 Electrical Conn.: Screw terminal
 Weight: 368 g (13 oz)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

RANGE		MODEL NO.	PRICE	COMPATIBLE METERS*
inH ₂ O	Pa/kPa			
0 to 0.1	0 to 25	PX655-0.1DI	\$495	DP25B-E, DP41-E, DP460-E
0 to 0.25	0 to 62	PX655-0.25DI	620	DP25B-E, DP41-E, DP460-E
0 to 0.50	0 to 125	PX655-0.5DI	425	DP25B-E, DP41-E, DP460-E
0 to 0.75	0 to 187	PX655-0.75DI	395	DP25B-E, DP41-E, DP460-E
0 to 1	0 to 249	PX655-01DI	395	DP25B-E, DP41-E, DP3002-E
0 to 1.5	0 to 374	PX655-01.5DI	395	DP25B-E, DP41-E, DP3002-E
0 to 2	0 to 498	PX655-02DI	395	DP25B-E, DP41-E, DP460-E
0 to 3	0 to 748	PX655-03DI	395	DP25B-E, DP41-E, DP460-E
0 to 5	0 to 1.25	PX655-05DI	395	DP25B-E, DP41-E, DP460-E
0 to 10	0 to 2.49	PX655-10DI	395	DP25B-E, DP41-E, DP3002-E
0 to 25	0 to 6.23	PX655-25DI	395	DP25B-E, DP41-E, DP460-E
0 to 50	0 to 12.5	PX655-50DI	395	DP25B-E, DP41-E, DP460-E
BIDIRECTIONAL RANGES				
±0.1	25	PX655-0.1BDI	\$455	DP25B-E, DP41-E, DP460-E
±0.25	62	PX655-0.25BDI	425	DP25B-E, DP41-E, DP460-E
±0.50	125	PX655-0.5BDI	395	DP25B-E, DP41-E, DP460-E
±1	249	PX655-01BDI	395	DP25B-E, DP41-E, DP460-E
±2.5	623	PX655-2.5BDI	395	DP25B-E, DP41-E, DP460-E
±5	1.25	PX655-05BDI	395	DP25B-E, DP41-E, DP460-E
±10	2.49	PX655-10BDI	395	DP25B-E, DP41-E, DP460-E
±25	6.23	PX655-25BDI	395	DP25B-E, DP41-E, DP460-E
±50	12.5	PX655-50BDI	395	DP25B-E, DP41-E, DP460-E

Comes with complete operator's manual.

* See section D for compatible meters.

Ordering Example: PX655-01DI, 0 to 1 inH₂O low-pressure differential pressure transmitter, \$395.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
OP-6	\$340	Reference Book: Fundamentals of Temperature, Pressure, and Air Flow Measurement

DIFFERENTIAL PRESSURE TRANSDUCERS
B



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters