

Four-Channel Data Logger Thermometer **NEW**

Includes USB and RS232 Cables

HH309A
£200



- ✓ 4 Type K Thermocouple Inputs
- ✓ Displays 4 Channels Simultaneously or 2 Channels with Delta
- ✓ Data Logger with 16,000 Records per Channel
- ✓ USB and RS232 Interface with Windows Software
- ✓ Real-Time Clock
- ✓ Auto Power-Off
- ✓ HOLD Function
- ✓ MAX/MIN Function
- ✓ Resolution 0.1°C/0.1°F
- ✓ Low Battery Indication

The HH309A is a small 4-input thermometer plus a powerful data logger. The unit can store up to 16,000 records per channel at programmed intervals. The REC button is used to start and stop recording. You can store as many data sets as you want until memory is full. The unit comes with Windows-based software (Windows 98, NT, XP, ME) for the display and saving of data.

Thermocouple Included!

This model includes a free 1 m (40") Type K insulated beaded wire thermocouple with subminiature connector and wire spool caddy (1 per channel).
Order a Spare!

Model No. SC-GG-KI-30-IM, £10.



USB and RS232 Interfaces



HH309A, £200, shown smaller than actual size.

Specifications

Range: -200 to 1370°C (-328 to 2498°F)

Typical Accuracy: ±0.2% rdg +1°C

Resolution: 0.1° between -200 and 200°C/F, else 1°C/F

Sample Rate: 3 seconds

Operating Conditions:

0 to 50°C (32 to 122°F)

0% to 80% RH (0 to 35°C, 32 to 95°F)

0% to 60% RH (35 to 50°C, 95 to 122°F)

Storage Temperature:

-20 to 60°C (-4 to 140°F)

Battery: 9 V (included)

Dimensions:

184 H x 64 W x 30 mm D

(7.25 x 2.5 x 1.2")

Weight: Approx 250 g (8.8 oz)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
HH309A	£200	4-channel data logger thermometer
SC-GG-KI-30-IM	10	Spare Type K thermocouple
HH300-ADAPTER-220VAC-UK	10	AC adaptor
HH300-CABLE	12	Spare RS232 interface cable
HH300-CABLE-USB	12	Spare USB interface cable
CAL-3-HH	50	Traceable calibration with points

Comes with 4 beaded wire Type K thermocouples (1 per input), USB and RS232 interface cables, software, carry case, battery, and instruction manual.

Ordering Example: HH309A, 4 input data logging thermometer, £200.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters