


High-Temperature Quick-Disconnect Thermocouples

NHX ceramic (high-purity alumina) connector rated to 650°C tube clamp provides extra strength.

ICSS-IM60G-300-NHX, £27, shown smaller than actual size.

Sheath available in Super OMEGA CLAD™ XL thermocouple in grounded, insulated and exposed junctions.

MEETS OR EXCEEDS
SPECIAL LIMITS
OF ERROR (SLE)
AND EN 60584-2:
Tolerance Class 1



Standard-Size Ceramic Plug

SUPER OMEGA CLAD™ XL HIGHLIGHTED!

To Order (Specify Model Number)							
Calibration IEC Code	Sheath† Material	Sheath Dia. mm	Upper Temp Guidelines °C T/C Junction	Model No. *Specify Junction (G)rounded, (E)xposed, or (U)ngrounded. **Probe Length 300 mm, 450 mm in Stock	Price 300 mm		Price Add'l 300 mm MI Cable
					G*/E*	U*	
K CHROMEGLA™ ALOMEGA™	304SS	1.5	899	CASS-IM15(*)-(**)-NHX	£24.50	£26.00	£1.05
	304SS	3.0	899	CASS-IM30(*)-(**)-NHX	24.50	26.00	1.25
	304SS	4.5	899	CASS-IM45(*)-(**)-NHX	25.00	26.50	2.10
	304SS	6.0	899	CASS-IM60(*)-(**)-NHX	27.00	28.50	3.40
	INC600	1.5	921	CAIN-IM15(*)-(**)-NHX	£24.50	£26.00	£1.05
	INC600	3.0	1071	CAIN-IM30(*)-(**)-NHX	24.50	26.00	2.10
	INC600	4.5	1149	CAIN-IM45(*)-(**)-NHX	25.00	26.50	2.90
	INC600	6.0	1149	CAIN-IM60(*)-(**)-NHX	27.00	28.50	5.00
	XL	1.5	1038	CAXL-IM15(*)-(**)-NHX	£26.50	£28.00	£1.15
	XL	3.0	1149	CAXL-IM30(*)-(**)-NHX	26.50	28.00	2.30
J IRON- CONSTANTAN	304SS	1.5	441	ICSS-IM15(*)-(**)-NHX	£24.50	£26.00	£1.05
	304SS	3.0	521	ICSS-IM30(*)-(**)-NHX	24.50	26.00	1.25
	304SS	4.5	621	ICSS-IM45(*)-(**)-NHX	25.00	26.50	2.10
	304SS	6.0	721	ICSS-IM60(*)-(**)-NHX	27.00	28.50	3.40
N OMEGA-P™-N™	XL	1.5	1038	NNXL-IM15(*)-(**)-NHX	£26.50	£28.00	1.15
	XL	3.0	1149	NNXL-IM30(*)-(**)-NHX	26.50	28.00	2.30
	XL	4.5	1204	NNXL-IM45(*)-(**)-NHX	27.00	28.50	3.20
	XL	6.0	1204	NNXL-IM60(*)-(**)-NHX	29.00	30.50	5.60

SCASS-IM300G-150-SHX, £22.50, shown smaller than actual size.



150 mm length standard*

Ceramic connector

Miniature Ceramic Plug

SUPER OMEGA CLAD™ XL HIGHLIGHTED!

To Order (Specify Model Number)							
Calibration IEC Code	Sheath† Material	Sheath Dia. mm	Upper Temp Guidelines °C T/C Junction	Model No. *Specify Junction (G)rounded, (E)xposed, or (U)ngrounded. **Probe Length 150 mm, 300 mm, in Stock	Price 150 mm		Price Add'l 150 mm MI Cable
					G*/E*	U*	
K CHROMEGLA™ ALOMEGA™	304SS	0.25	260	SCASS-IM025(*)-(**)-SHX	£38.50	£52.00	£0.85
	304SS	0.50	370	SCASS-IM050(*)-(**)-SHX	25.00	26.50	0.45
	304SS	0.75	370	SCASS-IM075(*)-(**)-SHX	25.00	26.50	0.45
	304SS	1.00	371	SCASS-IM100(*)-(**)-SHX	25.00	26.50	0.45
	304SS	1.50	899	SCASS-IM150(*)-(**)-SHX	22.50	23.75	0.55
	304SS	3.00	899	SCASS-IM300(*)-(**)-SHX	22.50	23.75	0.65
	XL	0.25	316	SCAXL-IM025(*)-(**)-SHX	£40.50	£54.00	£0.95
	XL	0.50	427	SCAXL-IM050(*)-(**)-SHX	27.00	28.50	0.45
	XL	0.75	427	SCAXL-IM075(*)-(**)-SHX	27.00	28.50	0.45
	XL	1.00	427	SCAXL-IM100(*)-(**)-SHX	27.00	28.50	0.45
J IRON- CONSTANTAN	304SS	0.25	204	SICSS-IM025(*)-(**)-SHX	£38.50	£52.00	£0.85
	304SS	0.50	260	SICSS-IM050(*)-(**)-SHX	25.00	26.50	0.45
	304SS	0.75	316	SICSS-IM075(*)-(**)-SHX	25.00	26.50	0.45
	304SS	1.00	371	SICSS-IM100(*)-(**)-SHX	25.00	26.50	0.45
	304SS	1.50	441	SICSS-IM150(*)-(**)-SHX	22.50	23.75	0.55
	304SS	3.00	521	SICSS-IM300(*)-(**)-SHX	22.50	23.75	0.65
N OMEGA-P™-N™	XL	0.50	427	SNNXL-IM050(*)-(**)-SHX	£27.00	£28.50	0.45
	XL	0.75	427	SNNXL-IM075(*)-(**)-SHX	27.00	28.50	0.45
	XL	1.00	427	SNNXL-IM100(*)-(**)-SHX	27.00	28.50	0.45
	XL	1.50	1038	SNNXL-IM150(*)-(**)-SHX	27.00	28.50	0.45
	304SS	3.00	1149	SNNXL-IM300(*)-(**)-SHX	24.50	26.00	1.15

* Other lengths available; consult Sales Department.

† To order with INCONEL® 600, 310SS, 316SS or 321SS sheath change "SS" in model number to "IN", "310SS", "316SS" or "321SS" respectively, no additional charge. Inconel® is a registered trademark of Huntington Alloys Canada Ltd.

Ordering Example: SCASS-IM150U-150-SHX, high-temperature miniature quick-disconnect probe, Type K, 304 SS sheath, 1.5 mm OD, insulated junction, 150 mm long, £23.75. SCAXL-IM050U-150-SHX, Type K, Super OMEGA CLAD™ XL sheath, 0.5 mm Dia., 150 mm long probe with miniature ceramic plug and mating connector, £28.50. Inconel® is a registered trademark of Huntington Alloys Canada Ltd





UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters