






# CABLE ASSEMBLIES

For Probes, Sensors and Transmitters

## M12C Series

- ✓ Standard M12 Female Connectors with Gold Plated Contacts
- ✓ 316 Stainless Steel Nut
- ✓ Straight or Right Angle Models
- ✓ PVC or Polyurethane Cables with Stripped Lead Termination
- ✓ Available in 5 m or 10 m Standard Lengths



**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)	
Model No.	Description
M12C-PUR-4(*)-F-2	Cable, M12, 4-pin female, polyurethane jacket, 2 m long
M12C-PVC-4(*)-F-5	Cable, M12, 4-pin female, PVC jacket, 5 m long
M12C-PUR-4(*)-F-5	Cable, M12, 4-pin female, polyurethane jacket, 5 m long
M12C-PVC-4(*)-F-10	Cable, M12, 4-pin female, PVC jacket, 10 m long
M12C-PUR-4(*)-F-10	Cable, M12, 4-pin female, polyurethane jacket, 10 m long

\* Specify connection: "-S" for straight, or "-R" for right angle, no additional charge.

Ordering Examples: M12C-PVC-4-R-F-5, M12C series cable assembly, 4-pin M12 female, right angle connection, PVC cable, 5 m L .

M12C-PUR-4-S-F-10, M12C series cable assembly, 4-pin M12 female, straight connection, polyurethane cable, 10 m L.

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters