


Thermocouple Probes

With M8 Moulded Connectors



**M8M Series
Starts at
£14**

- ✓ Type J and K Thermocouples
- ✓ Insulated Junctions
- ✓ -50 to 90°C Connector Temperature Range
- ✓ 304 Stainless Steel Probe (Type J) and Inconel® 600 Probe (Type K)
- ✓ Many Standard Lengths Available
- ✓ IP67 Moulded M8 Connector



Model Number	Price		Probe Length	Thermocouple Type	Sheath Material
	2 mm Dia	3 mm Dia			
M8MJSS-(*)-U-150	£14	£14	150 mm	J	304 SS
M8MJSS-(*)-U-200	14.75	14.75	200 mm	J	304 SS
M8MJSS-(*)-U-250	15.50	15.50	250 mm	J	304 SS
M8MKIN-(*)-U-150	14	14	150 mm	K	Inconel 600
M8MKIN-(*)-U-200	14.75	14.75	200 mm	K	Inconel 600
M8MKIN-(*)-U-250	15.50	15.50	250 mm	K	Inconel 600

(*) Insert "M2" for 2 mm or "M3" for 3 mm probe diameter.

Ordering Examples: M8MJSS-M3-U-150, 3 mm diameter by 150 mm long, Type J thermocouple with 304 stainless steel sheath and moulded M8 connector, £14.

M8MKIN-M3-U-250, 3 mm diameter by 250 mm long, Type K thermocouple with Inconel 60 sheath and moulded M8 connector, £15.50

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters