

Programmable Timer



PTC-16
£89



- ✓ 9 Programmable Modes
- ✓ 6 Timing Ranges
- ✓ Security Code
- ✓ 2- or 1-Timed plus 1 Instantaneous Contact
- ✓ Programmable Reset Function
- ✓ External Hold and Reset
- ✓ Selectable Up/Down Timing
- ✓ LED Status and Timing Indicators



PANEL METERS

The PTC-16 timer has all of the features of the PTC-14 panel-mount timer in a DIN rail mounting package. The PTC-16 covers time ranges from 0.1 seconds to 100 hours in a single model and has nine operating modes, two power supply options, and two timed relay outputs. When only one timed output is being used, the other output acts as a set of instantaneous changeover contacts.

PTC-16, £89, shown larger than actual size.



Specifications

Timing Ranges: 0 to 999.9 sec, 0 to 9999 sec, 0 to 9999 min, 0 to 99 min 59 sec, 0 to 99 hr 59 min, 23:59 in 24 hr clock mode

Timing Modes: DE, DDE, DP, CCT, DE-2, IT-2, DE-IT, DD-2, 24HR

Supply Voltage: 110 Vac and 230 Vac 50/60 Hz or 12 to 24 Vac/Vdc

Supply Variation: ±10% of supply voltage

Battery Backup: External 3 Vdc to retain clock on 24 hr mode only at loss of supply voltage

Power Drain: 3 Va max

Contact Ratings:

OP1: 8 A @ 240 Vac, SPDT

OP2: 5 A @ 240 Vac resistive, SPST

Reset Time: 100 msec max


Ambient Conditions:

Working Temp: 0 to 50°C (32 to 122°F)

Storage Temp: 0 to 70°C (32 to 158°F)

Approvals: Complies with CE directives EN50081-1 and EN50082-1 for EMC and EN61010-1 for low voltage

Weight: 240 g (8.5 oz)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
PTC-16	£89	Programmable timer, AC voltage
PTC-16-LV	89	Programmable timer, low voltage
OP-17	10	Reference Book: Measure for Measure

Comes with complete operator's manual.
Ordering Example: PTC-16-LV, programmable timer, low voltage, £89.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters