

# Food Service Thermometer



HANDHELDS

**WATERPROOF!**

- ✓ Simple to Operate
- ✓ Waterproof Case
- ✓ "T" Type and Thermistor Models
- ✓ Long Battery Life (Typically 500 Hours), Battery Included
- ✓ Rugged Case for Use in Harsh Environments
- ✓ Ergonomic Design
- ✓ Magnified Backlit Digital Display
- ✓ "Hold" Function
- ✓ Models are in °F or °C Settings
- ✓ Isolated Battery Compartment

Model HH2146TF  
Starts at  
**£97**



The HH2106T and HH2146T build on the success of the HH2000 series thermometers.

This new generation marks an evolutionary step in the development of OMEGA's digital thermometers and probes. These thermometers are completely waterproof and incorporate the Food Industry standard Lumberg connector for thermistor and thermocouple probes.

THX-HH2146T Penetration probe, £27, sold separately. See ordering chart below.



## Specifications

### General

**Battery:** Two AA size

**Dimensions:** 155 x 65 x 35 mm (6.1 x 2.5 x 1.4")

**Weight:** 250 g (8 oz)

**HH2146TC/HH2146TF**

**Sensor Type:** Thermistor, THX-HH2146T

**Connector Type:** Lumberg

**Setting:** HH2146TC reads in °C; HH2146TF reads in °F

**Instrument Accuracy:** ±0.5°C (0.4°F) over range -20 to 70°C (-4 to 158°F), ±0.8°C (1.4°F) elsewhere

**Hold Function:** Yes

**Range:** -40 to 120°C (-40 to 248°F)

**HH2106TC/HH2106TF**

**Sensor Type:** Type T thermocouple, THX-HH2106T

**Connector Type:** Lumberg


**Setting:** HH2106TC reads in °C; HH2106TF reads in °F

**Instrument Accuracy:** ±0.2°C (0.4°F) over range -20 to 70°C (-4 to 158°F), ±0.1% rdg, ±0.2°C (0.4°F) elsewhere

**Hold Function:** Yes

**Range:** -250 to 400°C (-418 to 752°F)

### Probe Dimensions mm (inches)



**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

### To Order (Specify Model No.)

Model No.	Price	Description
HH2146TC	£97	Series 400 thermistor handheld thermometer, °C
HH2146TF	97	Series 400 thermistor handheld thermometer, °F
HH2106TC	114	Type T handheld thermometer, °C
HH2106TF	114	Type T handheld thermometer, °F
CAL-3-HH	50	Traceable calibration certificate

Each unit comes with batteries, rubber holster and operator's manual. Order probe separately below.

**Ordering Example:** HH2146TC plus THX-HH2146T is a handheld thermometer in °C, thermistor sensor type with penetration probe, £97 + 27 = £124.

### Probes

Model No.	Price	Description
THX-HH2146T	£27.00	Penetration probe (for HH2146TC or HH2146TF)
THX-HH2106T	33.50	Penetration probe (for HH2106TC or HH2106TF)