


Non-Reversible OMEGALABEL® Temperature Labels TL-8 and 10 Range Series

- ✓ Adhesive Backs for Easy Mounting for Temperatures Above -40°C/°F
- ✓ Indicator Turns Black When Exposed

Applications:

- General • Aeronautical • Electrical • HVAC
- All applications where size is not a conditioning factor

8-Temperature Range Labels
TL-8 SERIES 46 x 18 mm



Shown
actual size

Model No.	Temperature Range									
TL-8-105(*)	°F	105	110	115	120	130	140	150	160	
	°C	40	43	46	49	54	60	66	71	
TL-8-170(*)	°F	170	180	190	200	210	220	230	240	
	°C	77	82	88	93	99	104	110	116	
TL-8-250(*)	°F	250	260	270	280	290	300	310	320	
	°C	121	127	132	138	143	149	154	160	
TL-8-330(*)	°F	330	340	350	360	370	380	390	400	
	°C	166	171	177	182	188	193	199	204	
TL-8-410(*)	°F	410	420	435	450	465	480	490	500	
	°C	210	216	224	232	241	249	254	260	

Price
pk of 10 pk of 30
£870 £24⁰⁰


*Insert "-10" for pack of 10 or
"-30" for pack of 30.

Ordering Example: TL-8-170-30
Eight Temperature Range Labels (170, 180, 190,
200, 210, 220, 230, 240°F), pack of 30; £24.



Confirm correct
shipping of critical
products.

10-Temperature Range Labels
TL-10 SERIES 54 x 18 mm



Shown
actual size

Model No.	Temperature Range									
TL-10-105(*)	°F	105	110	115	120	130	140	150	160	170 180
	°C	40	43	46	49	54	60	66	71	77 82
TL-10-190(*)	°F	190	200	210	220	230	240	250	260	270 280
	°C	88	93	99	104	110	116	121	127	132 138
TL-10-290(*)	°F	290	300	310	320	330	340	350	360	370 380
	°C	143	149	154	160	166	171	177	182	188 193
TL-10-390(*)	°F	390	400	410	420	435	450	465	480	490 500
	°C	199	204	210	216	224	232	241	249	254 260

Price
pk of 10 pk of 30
£900 £24⁷⁵


*Insert "-10" for pack of 10 or "-30" for pack of 30.

Ordering Example: TL-10-105-30
Ten Temperature Range Labels (105, 110, 115,
120, 130, 140, 150, 160, 170, 180°F),
pack of 30; £24.75

ALL MODELS AVAILABLE FOR FAST DELIVERY!

Discount Schedule (Packs)

1-9	Net
10-49	10%
50-99	20%
100-499	30%
500+	Consult Sales



Test PC Board
Components

Shown
actual size



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters