

OMEGALUX™ ROPE HEATERS



FGR Series
Starts at

£8

- ✓ Operating Temperature Rating to 482°C
- ✓ Wraps Around Small Diameter Pipes and Tubes

OMEGALUX™ rope heaters apply heat to tubing with diameters as small as 3.2 mm. Featuring a maximum allowable operating temperature of 482°C, the FGR Series rope heaters can be wrapped around either conductive or non-conductive surfaces. Each end terminates with 600 mm long fibreglass-insulated lead wire.


SPECIFICATIONS

Maximum Allowable Temperature: 482°C
Suitable for Use on Conductive Surface: Yes
Resists Moisture Vapour or Chemicals: No
Standard Diameter: 5 mm
Voltage: 120Vac or Vdc, 240V optional
Linear Wattage: 4 Watts/in
Heater Length: 0.9, 1.8, 2.4 or 3.0 m
Lead Length: 600 mm
Termination: Stripped leads

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)				
Model Number	Description Length	Wattage	Voltage	Price
FGR-030	0.9 m	125	120	£8.00
FGR-060	1.8 m	250	120	18.75
FGR-080	2.4 m	400	120	20.00
FGR-100	3.0 m	500	120	27.50

240 Vac models and other wattages also available.
 For 240V models add "/240V" to end of model number, same price as 120V units.
Ordering Example: FGR-060/240, 1.8 m 240 Vac rope heater, £18.75.



ELECTRIC HEATERS

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters