

ENHANCED MODULAR CONTROLLER SERIES MASTER



Starts at
\$499



- Adds Multiple Protocol Conversion Functionality to Data Acquisition and Multi-Zone PID Control Applications
- Performs Hierarchical Control of Other Modules in the Modular Controller Series
- Stores Module Configuration Information, and Automatically Reprograms Replaced Modules
- Extensive Built-In Driver List Allows Easy Data Mapping to PLCs, PCs, and SCADA Systems
- Independent Serial Ports Provide Virtually Unlimited Integration Methods
- 10 Base-T/100 Base-TX Ethernet Connection Provides Networking Capability
- Supports up to 16 Modular Controller Series Modules
- Supports up to 9 Protocols Simultaneously (With Expansion Card)

The Model CSMSTRLE is a communications and control platform designed for use with Modular Controller Series slave modules. The CSMSTR uses a proprietary high speed serial protocol to communicate, via backplane connection, with up to 16 slave modules. Through the same connection, the Master also provides power to the modules.

When powered up, the CSMSTR automatically identifies and addresses connected slave modules. By storing the configuration information of all of the modules, the CSMSTR is able to automatically configure modules if they are replaced.

The Master provides high-speed RS232/422/485 communication ports and an Ethernet port for connection to PCs, PLCs, and SCADA systems. An extensive list of master and slave protocol drivers are available to allow the CSMSTR to share and exchange variable data with external devices. The 10 Base-T/100Base-TX Ethernet port can also be used to connect and share data with other devices at high speeds.

The design of the Modular Controller Series high density packaging and DIN rail mounting saves time and panel space. The controller snaps easily onto standard top hat (T) profile DIN rail.

The CSMSTR is programmed with Crimson 2.0 software for Windows® 2000 or later platforms. The software is an easy to use, graphical interface which provides a means of communication configuration, as well as commissioning and calibration of new systems.

SPECIFICATIONS

Power: 24 Vdc \pm 10% 400 mA min. (1 module)
3.5A max. (16 modules + expansion Card)
must use class 2 or SELV rated power supply.



CSMSTRLE, \$499,
shown smaller than
actual size.

Communications:

USB/PG Port: Adheres to USB specification 1.1. Device only using Type B connection

Serial Ports: Format and Baud Rates for each port are individually software programmable up to 115,200 baud.

RS232/PG Port: RS232 port via RJ12

COMMS Ports: RS422/485 port via RJ45, and RS232 port via RJ12

DH485 TXEN: Transmit enable; open collector, V_{OH} = 15 VDC, V_{OL} = 0.5 V @ 25 mA max.

Ethernet Port: 10 BASE-T / 100 BASE-TX RJ45 jack is wired as a NIC (Network Interface Card)

LEDs:

STS: Status LED indicates condition of master.

TX/RX: Transmit/Receive LEDs show serial activity.

Ethernet: Link and activity LEDs.

CF: Compactflash LED indicates card status and read/write activity

Memory:

On-Board User Memory: 4 Mbytes of non-volatile flash memory

On-Board SDRAM: 2 Mbytes

Memory Card: Compactflash type II slot for type I and type II cards (Used for optional database storage only)

Real Time Clock: Typical accuracy is less than one minute per month drift

Battery: Lithium coin cell (included). Typical lifetime of 10 years at 25 °C (77°F)



Environmental Conditions:

Operating Temperature Range:

0 to 50°C (32 to 122°F)

Storage Temperature Range:

-30 to +70°C (-22 to 158°F)

Operating and Storage Humidity:

80% max relative humidity,
non-condensing, from
0 to 50°C (32 to 122°F)

Vibration According to IEC 68-2-6:

5 to 150 Hz, in X, Y, Z direction for
1.5 hours, 2 g's

Shock According to IEC 68-2-27:

Operational 25g, 11ms in 3 directions.

Altitude: Up to 2000 meters

Construction: Case body is burgundy high impact plastic and stainless steel.

Installation category I, pollution degree 2

Power Connection: Removable wire clamp screw terminal block

Wire Gage Capacity: 24 AWG to 12 AWG

Torque: 4.45 to 5.34 in/lb (0.5 to 0.6 N-m)

Mounting: Snaps onto standard DIN style top hat (T) profile mounting rails according to EN50022 -35 x 7.5 and -35 x 15

Certification and Compliances:

Safety:

UL Listed: File #E302106, UL508, CSA 22.2 No. 14-M05 LISTED by Und. Lab. Inc. to U.S. and Canadian safety standards IEC 61010-1, EN 61010-1: Safety requirements for electrical equipment for measurement, control, and laboratory use, Part 1

Electromagnetic Compatibility:

Emissions and Immunity to EN 61326:

Electrical equipment for measurement, control and laboratory use

Immunity to Industrial Locations*:

Electrostatic discharge EN 61000-4-2
Criterion A 2

4 kV contact discharge

8 kV air discharge

Electromagnetic RF fields EN 61000-4-3
Criterion A 10 V/m

Fast transients (burst) EN 61000-4-4
Criterion A

2 kV power

2 kV signal

Surge EN 61000-4-5 Criterion A

1kV L-L, 2 kV L-N-E power

RF conducted interference EN 61000-4-6
Criterion A

3 V/rms

Emissions:

Emissions EN 55011 Class A

Weight: 456.4 g (15.1 oz)

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	MASTER MODULE DESCRIPTION
CSMSTRLE	\$499	Modular controller master, multiple protocol converter (only)
SFCRM2MC	62	Modular controller crimson programming software, manual and download cable

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
G3CF064M	\$90	64 MB compact flash card (industrial grade 2 million write cycles)
G3CF256M	235	256 MB compact flash card (industrial grade 2 million write cycles)
G3CF512M	368	512 MB compact flash card (industrial grade 2 million write cycles)
CBLPROG0	41	Programming cable for CS, G3, and paradigm
CBLUSB00	26	USB programming cable for G3, DSP and modular controller, type A-B
PSDR0100	129	Mini power supply 1A
PSDR0200	159	Mini power supply 2A
PSDR0400	199	Mini power supply 4A
RSRSTP00	5	Rail stops (qty 2)
CSTERM00	10	Replacement termination plug
CSBASE00	31	Replacement base
CSTERM00	10	Replacement termination plug

MODULES

MODEL NO.	PRICE	MODULE DESCRIPTION
CSDIO14R	\$247	8-inputs 6 relay outputs
CSDIO14S	247	8-inputs 6 solid state outputs
CSINV800	536	8-channel ± 10 V input module
CSINI800	536	8-channel 0(4) to 20 mA input module
CSOUT400	280	4-channel analog output
CSPID1R0	227	Single loop module, relay outputs
CSPID1RA	247	Single loop module, relay outputs, analog output
CSPID1RM	247	Single loop module, relay outputs, heater current input
CSPID1S0	227	Single loop module, solid state outputs
CSPID1SA	247	Single loop module, solid state out. Analog output
CSPID1SM	247	Single loop module, solid state, heater current input
CSPID1TA	247	Single loop module, triac outputs, analog output
CSPID2R0	340	Dual loop module, relay outputs
CSPID2RM	371	Dual loop module, relay outputs, heater current input
CSPID2S0	340	Dual loop module, solid state outputs
CSPID2SM	371	Dual loop module, solid state outputs, heater current input
CSPID2T0	340	Dual loop module, triac outputs
CSPID2TM	371	Dual loop module, triac outputs, heater current input
CSRTD600	402	6-channel input, RTD
CSSG10RA	320	Single loop, 1 strain gage input, relay outputs, analog out
CSSG10SA	320	Single loop, 1 strain gage input, solid state out, analog out
CSSG11RA	400	Single loop, 2 strain gage input, relay outputs, analog out
CSSG11SA	400	Single loop, 2 strain gage input, solid state out, analog out
CSTC8000	536	8-channel thermocouple module

Controllers come with termination plug, terminal power block, and complete operator's manual.
Ordering Example: CSMSTRLE, controller, SFCRM2MC, software, G3CF512M, 512 MB flash card, CSDIO14R, 8 inputs 6 relay output module, PSDR0100, power supply,
\$499 + 99 + 368 + 247 + 129 = **\$1342.**

*Notes:

1. Criterion A: Normal operation within specified limits.

2. This device was designed for installation in an enclosure. To avoid electrostatic discharge to the unit in environments with static levels above 4 kV, precautions should be taken when the device is mounted outside an enclosure. When working in an enclosure (ex. making adjustments, setting jumpers etc.), typical anti-static precautions should be observed before touching the unit.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters