

# NEMA TYPE 4 ENVIROLINE® JUNCTION ENCLOSURES WITH VIEWING WINDOW



## SCE-ELJW Series



SCE-1614ELJW smaller than actual size.

- 0.063" Thick Carbon Steel
- Also Available in 304 and 316 Stainless Steel
- Seams Continuously Welded and Ground Smooth
- Flange Trough Collar Around All Sides of Door Opening
- Oil-Resistant Gasket
- Standoffs Provided for Mounting Optional Sub-Panels
- Removable Hinges
- Doors Open 180°
- Black Mini-Quarter Turn Latches
- Optional Latches Available
- Latches Opened/Closed with a Screwdriver
- Sealing Washers, Hole Plugs and Mounting Feet Included
- Ground Stud on Door and Body

## Application


Designed to house electrical controls, instruments and components that require unrestricted viewing of the gauges or controls in areas which may be regularly hosed down or are in very wet or oily conditions. Provides protection from dust, dirt, oil, and water.

## Finish

ANSI-61 gray powder coat inside and out. Optional Subpanels are powder coated white.

## Industry Standards IS2

NEMA Type 4 and 12  
UL Type 4 and 12  
CSA Type 4 and 12  
IEC 60529 IP66



**LATCH NOTES:**  
 One latch centered on the door vertically if height is ≤356 (14)  
 Two latches located 76 (3) from top and bottom of door if height is ≥356 (14)

To Order Visit <a href="http://omega.com/sce-eljw">omega.com/sce-eljw</a> for Pricing and Details							
ENCLOSURE		DIMENSIONS (inch)				SUB-PANEL	
MODEL NO.	HEIGHT (A)	WIDTH (B)	DEPTH (C)	VIEWING WINDOW	MODEL NO.	HEIGHT (D)	WIDTH (E)
SCE-1008ELJW	10	8	4	6.0 x 3.38	SCE-10P8J	9.25	7.25
SCE-10086ELJW	10	8	6	6.0 x 3.38	SCE-10P8J	9.25	7.25
SCE-1210ELJW	12	10	6	8.0 x 5.38	SCE-12P10J	11.25	9.25
SCE-12108ELJW	12	10	8	8.0 x 5.38	SCE-12P10J	11.25	9.25
SCE-1614ELJW	16	14	6	12.0 x 9.38	SCE-16P14J	15.25	13.25
SCE-16148ELJW	16	14	8	12.0 x 9.38	SCE-16P14J	15.25	13.25
SCE-20208ELJW	20	20	8	16.0 x 15.38	SCE-20P20J	19.25	19.25

Ordering Examples: SCE-10086ELJW NEMA Type 4 enclosure with viewing window, 10 H x 8 W x 6" D.  
 SCE-16148ELJW NEMA Type 4 enclosure with viewing window, 16 H x 14 W x 8" D.