



The Mini NOMAD® Series

Miniature RFID Data Loggers and Readers: Economical, Fast, Accurate **Wireless** Data Retrieval and Storage

**Weather
Resistant!**

OM-84 Matchbook™ Series
Starts at
£60
5-Pack



The OM-84, £60, features a miniature, water resistant design and a factory replaceable battery.

Write-On-Window!

OMEGA's miniature RFID data loggers feature a unique write-on-window built into every unit. This provides an easy way to add your own tracking or shipment number to each unit for easy identification after retrieval from deployment!

Shown actual size.

- ✔ Ideal Solution for Cold Chain Monitoring
- ✔ Factory Replaceable Batteries
- ✔ Accurate Up to $\pm 0.5^{\circ}\text{C}$ (1°F)
- ✔ Wireless RFID Technology
- ✔ Store Up to 10,000 Individual Readings
- ✔ Save Stored Data From Each Logger Into Your Computer with Included Software
- ✔ Low Power Operation and Sleep Mode
- ✔ Pre-Packaged for Moderate High Volume Discounts

PATENTS PENDING



OM-80-RD1, reader, £131, shown reading, downloading and storing data from an OM-84-TMP, temperature data logger, £60 (sold in packs of 5).

Laptop not included.

OMEGA's OM-80 Series of data loggers have been engineered to provide an economical and reliable solution for cold chain environmental monitoring. The lower cost OM-84 features a miniature weather-resistant design with a factory replaceable battery. Operates over a wide range of temperatures from -40 to 60°C making them ideal for


most remote data logging applications inside shipping containers. Built-in LEDs display high and low alarm verification indicating that measured temperatures have remained within the user programmable alarm window throughout deployment. An internal solid-state precision temperature sensor provides accurate readings up to $\pm 0.5^{\circ}\text{C}$.

**Save
Money!**

Factory Battery Replacement Service Did you know that you can recycle your OM-84 data loggers that have dead batteries? Send them back to OMEGA and we will install a fresh battery, reseal the package, check operation and send the unit back to you, all for a small fee. It's cheaper than buying a new one! This option is only available for Model OM-84 units and requires that you send back a minimum of 25 units. Please contact our Customer Service Department to request an AR number. Visit omega.co.uk/rfid for more information.

Miniature RFID Data Loggers

**“Deploy multiple units for better zone profiling...
All for less than the cost of one standard data logger”**



Specifications (Preliminary)

(Please visit omega.co.uk/rfid for the latest features and specifications)

Temperature Measurement Range: -40 to 60°C (-40 to 140°F)

Accuracy: ±0.5°C from 0 to 50°C (±1°C below 0°C or above 50°C)

Resolution: 0.1°C or °F

Storage Temperature: -40 to 85°C

Read/Write Wireless Range: Up to 50 mm

Power

OM-84-TMP: Lithium/manganese dioxide 3 volt coin cell (factory replaceable only)

Shelf Life: Up to 3 years (non-activated) with proper storage

Usage Life: Up to 2 years (after activation)

Memory: Up to 10,000 rdgs (eg: 208 days at 1 rdg/30 min)

Recording Programmable Interval: From 1 sec to 9 hrs, 6 min, 7 sec

Data Logging Start Time: Alarm clock or delayed start, selectable by user

Operation Status Indicator:

LED blinks green when the unit is activated

Alarm Status Indicator: LED blinks red when the unit exceeds high or low alarm set point

Activation: Push-button on surface of device

Temperature Alarm: Programmable temperature alarm with high and low limits, selectable in software

Dimensions:

OM-84: 61 L x 43 W x 6.4 mm H

 **MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)		
Model No.	Price	Description
OM-84-TMP-5	£60	Water resistant temperature logger, pack of 5
OM-84-TMP-20	229	Water resistant temperature logger, pack of 20
OM-84-TMP-50	545	Water resistant temperature logger, pack of 50
OM-84-TMP-100	1025	Water resistant temperature logger, pack of 100
OM-84-TMP-KIT*	199	Water resistant temperature logging kit: 5 loggers, benchtop reader, software, cable, case, marker
OM-80-RD1	131	Benchtop reader with software and USB cable
SC-HH500	8	Reader carrying case

* Comes complete with data loggers, benchtop reader unit, USB cable, software program on CD-ROM, permanent marker, easy operating instructions and batteries.

Ordering Examples: OM-84-TMP-5, temperature data logger (5-pack), OM-80-RD1, benchtop USB reader with cable and software, and SC-HH500 reader carrying case, £60 + 131 + 8 = £199.

OM-84-TMP-KIT, temperature logging kit, £199.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters