




**Thermocouple Data Logger with Extended Memory
Part of the NOMAD® Family**

OM-CP-TC110-2MB
Starts at
\$299



OM-CP-TC110-2MB data logger, \$299, shown larger than actual size.

- ✓ Wide Temperature Range
- ✓ Accepts Thermocouple Types J, K, T, E, R, S, B, N
- ✓ High Speed Download
- ✓ NIST Traceable
- ✓ Real-Time Operation
- ✓ Programmable Start Time
- ✓ Miniature Size

The OM-CP-TC110-2MB is a miniature, battery powered, stand alone, thermocouple based temperature data logger.

The OM-CP-TC110-2MB features a real-time clock module that extends the battery life to >2 years and allows for high speed downloads.

This is an all-in-one compact, portable, easy to use device that will measure and record up to 262,144 measurements per channel.

The storage medium is non-volatile solid state memory, providing maximum data security even if the battery becomes discharged. The device can be started and stopped directly from your computer and its small size allows it to fit almost anywhere.

The OM-CP-TC110-2MB makes data retrieval quick and easy. Simply plug it into an empty COM or USB port and our user-friendly software does the rest.

Type	Range	Resolution	Accuracy*
J	-210 to 760°C	0.1°C	±0.5°C
K	-270 to 1370°C	0.1°C	±0.5°C
T	-270 to 400°C	0.1°C	±0.5°C
E	-270 to 980°C	0.1°C	±0.5°C
R	-50 to 1760°C	0.5°C	±2.0°C
S	-50 to 1760°C	0.5°C	±2.0°C
B	50 to 1820°C	0.5°C	±2.0°C
N	-270 to 1300°C	0.1°C	±0.5°C

* Accuracy does not include errors due to thermocouple.

Specifications

INTERNAL CHANNEL

Temperature Range:

-40 to 80°C (-40 to 176°F)

Temperature Resolution: 0.1°C

Calibrated Accuracy: ±0.5°C (0 to 50°C)

REMOTE CHANNEL

Thermocouple Types:

J, K, T, E, R, S, B, N

Thermocouple Connection:

Female subminiature (SMP)

Cold Junction Compensation:

Automatic, based on internal channel

Maximum Thermocouple

Resistance: 1000Ω, <100Ω recommended

Start Time: Software programmable immediate start or delay start up to six months in advance

Real Time Recording: May be used with PC to monitor and record data in real time

Memory: 262,144 readings per channel for a total of 524,288 readings; software configurable memory wrap

Reading Rate: 1 reading every 2 seconds to 1 every 24 hours

Calibration: Digital calibration through software

Calibration Date: Automatically recorded within device


Battery Type: 3.6 V lithium battery (included), user replaceable

Battery Life: 2 years (5 minute reading rate at 25°C)

Data Format: Date and time stamped °C, °F, K, °R

Time Accuracy: ±1 minute/month (at 20 to 30°C)

OM-CP-IFC110, \$99, Windows software displays data in graphical or tabular format



Computer Interface: PC serial or USB (interface cable required); 57,600 baud

Software: WIN98/NT/2000/XP/VISTA 32-bit (VISTA 32-bit version only; VISTA 64-bit is not supported)

Operating Environment:

-40 to 80°C (-40 to 176°F)

0 to 95%RH non-condensing

Dimensions: 44 x 59 x 21 mm (1.7 x 2.3 x 0.8")

Weight: 35 g (1.3 oz)

5SRTC/5LRTC Series starts at \$48/5 pk, see omega.com for details.



OM-CP-TC110-2MB, data logger, \$299, shown actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-CP-TC110-2MB	\$299	Thermocouple data logger with extended memory
OM-CP-TC110-2MB-CERT	359	Thermocouple data logger with extended memory and NIST calibration certificate
OM-CP-IFC110	99	Windows software and 1.2 m (4') RS-232 cable with DB9F termination
OM-CP-IFC200	119	Windows software and 3.7 m (12') USB interface cable
OM-CP-BAT105	12	Replacement 3.6 V lithium battery

Comes with complete operator's manual, 3V lithium battery and RS-232 cable. The OM-CP-IFC110 Windows software includes required RS-232 to operate the data logger (sold separately).

Ordering Example: OM-CP-TC110-2MB-CERT, thermocouple recorder with NIST calibration certificate and OM-CP-IFC110, Windows software, \$359 + 99 = \$458.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters