

Temperature, Humidity and Dew Point Data Logger with LCD Display

OM-EL-USB-2-LCD

£65



- ✓ 0 to 100% RH Measurement Range
- ✓ -35 to 80°C (-31 to 176°F)
- ✓ Temperature Measurement Range
- ✓ Dew Point Indication via Windows® Control Software
- ✓ USB Interface for Set-Up and Data Download
- ✓ User-Programmable Alarm Thresholds for Temperature and %RH
- ✓ Status Indication via Red and Green LEDs
- ✓ High Contrast LCD, with 2½ Digit Temperature and Humidity Display Function
- ✓ Immediate, Delayed and Push-to-Start Logging
- ✓ Supplied Complete with Replaceable Internal Lithium Battery and Windows Control Software

The OM-EL-USB-2-LCD is a standalone data logger that measures and stores up to 16,379 relative humidity and 16,379 temperature readings over 0 to 100% RH and -35 to 80°C (-31 to 176°F) measurement ranges. The high contrast LCD can show a variety of temperature and humidity information.

At the touch of a button, the user can cycle between the current temperature and humidity, along with the maximum and minimum stored values for temperature and humidity. In addition, logging and alarm status is shown using two high intensity LEDs. The data logger is supplied with a long-life lithium battery, which can typically allow logging for up to 1 year.

The user can easily set up the data logger and download logged data by plugging the unit into a PC's USB port and using the supplied Windows software. Data logger parameters that can be set up include data logger name, °C or °F temperature units, logging rate (10 sec, 1 min, 5 min, 30 min, 1 hr, 6 hrs, 12 hrs), high and low alarms, immediate, delayed or push-to-start logging, display off, on for 30 seconds after button press, or permanently on, and data rollover (allows unlimited logging periods by overwriting the oldest data when the memory is full). Downloaded relative humidity, temperature and dew point data saved in text format can be graphed, printed and exported to other applications for further analysis.

SPECIFICATIONS

TEMPERATURE


Range: -35 to 80°C (-31 to 176°F)
Repeatability: ±0.1°C (±0.2°F)
Resolution: 0.5°C (1.0°F)
Accuracy: ±0.5°C (±1.0°F) typical;
 ±2.0°C (±4.0°F) max

HUMIDITY

Range: 0 to 100% RH
Repeatability: ±0.1% RH (short term)
Resolution: 0.5% RH
Accuracy (20 to 80% RH): ±3.0% RH typical;
 ±6.0% RH max

DEW POINT

Accuracy (Overall Error in the Calculated Dew Point, for RH Measurements Between 40 to 100 %RH @ 25°): ±1.1°C (±2°F)



OM-EL-USB-2-LCD, £65, shown actual size.




Comes with Windows control software.

GENERAL

Memory: 16,379 temperature and 16,379 relative humidity readings
Logging Interval: 10 sec to 12 hrs
Software: Windows 2000, XP (home and professional editions) and Vista (32-bit)
Operating Temperature Range: -35 to 80°C (-31 to 176°F); at temperatures below -20°C (-4°F) the LCD display will exhibit slower response times of approx 10 seconds
Alarm Thresholds: High/low alarm thresholds for %RH and temperature selectable in software
Start Date/Time: Selectable in software
Status Indicators (LEDs): Red and green
Power: ½ AA, 3.6V lithium battery (included)
Battery Life: 1 year typical (depends on sample rate, ambient temperature and use of LCD display)
Weight: 40 g (1.4 oz)
Dimensions: See dimensional drawing below

Dimensions: mm (in)



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OM-EL-USB-2-LCD	£65	Temperature, humidity and dew point data logger with LCD display
OM-EL-BATT	2.70	Replacement 3.6V lithium battery

Comes complete with Windows software on CD-ROM, protective cap and 3.6V lithium battery.

Ordering Example: OM-EL-USB-2-LCD, temperature/humidity data logger with LCD display, £65.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters