

Sensor Power Supply Module



PSM-2 Series

\$160



Basic Unit


- ✓ Field Sensor Power - Current Loops and/or Voltage Excitation Source
- ✓ Powered from System Batteries or External Power
- ✓ Installs into OM-320, OMP-MNL and OMP-MODL Data Logging Systems
- ✓ Control Input for ON/OFF Output Control via Software
- ✓ Field Programmable Output Voltages: 5, 10, 15 and 24 Vdc
- ✓ Low Power Design for Optimum Battery Life

The PSM-2 Power Supply Module provides excitation power for sensors used with the OM-320, OMP-MNL and OMP-MODL dataloggers. The PSM-2 can supply 100 mA of current ... sufficient to power up to five 4 to 20 mA loops. Alternatively it can be used as a voltage source for sensor excitation. A 5 Vdc output is standard and one additional output is available which can be jumper programmed in the field for 10, 15 or 24 Vdc output.

Four standard versions of the PSM-2 are available for use with the OM-320, OMP-MNL and OMP-MODL dataloggers or as a stand-alone module. The PSM-2 draws its power from the standard datalogger D-cells or an external supply. The PSM-2 outputs are cycled ON/OFF by a software controlled low-level 5 Vdc input from the associated datalogger which provides power only as required for sampling and minimizes power consumption and maximizes battery life. An LED indicator lights when the outputs are ON. Sensor excitation is easily programmed into the datalogger via the HyperWare software supplied with the datalogger.

Specifications

Terminal Strip: 12 position strip for



Model OM-320-PSM-2
Shown smaller than actual size

connection of external power input, control signal input and the programmable and 5 Vdc outputs and ground

Pigtail Connection: a pair of pigtails is provided for direct interface to the OM-320, OMP-MNL and OMP-MODL battery pack; in the OMP-MNL and OMP-MODL, the PSM-2 is wired in series between the battery pack (OMP-MNL-BATT) and the CPU module using the two provided pigtails and mating polarized connectors

Output Indication: output "ON" LED indicator

External Power Input: 8 to 32 Vdc input

Control Signal Input: field programmable for high input = ON or low input = ON; low = 0 to 0.5 Vdc; high = 3 to 20 Vdc; control current = 400 μ A at 5 Vdc (On)

Output No. 1 (Programmable): jumper selectable for 10, 15 or 24 Vdc range; accuracy; \pm 300 mV; current; 100 mA

Output No. 2 (Fixed): 5 Vdc; accuracy; \pm 150 mV; current; 40 mA

Parasitic Current (Outputs Off): 300 μ A typical

Circuit Protection: continuous short circuit protection on outputs; reverse polarity protection on inputs

Operating Temperature: -40 to 70°C (-40 to 158°F)

To Order (Specify Model Number)

Model No.	Price	Description
OM-320-PSM-2	\$160	Metal case housed stand-alone module for door mounted installation into the OM-320 datalogger
OMP-MNL-PSM-2	142	Power supply module mounted into OMP-MODL stacking frame for installation into the OMP-MNL or OMP-MODL datalogger stacks. Typically specified if sensor power is desired but the OMP-MNL-BATT (six D-cell battery pack) module is not.
OMP-MNL-BATT-PSM-2	210	Power supply module incorporated into the OMP-MNL-BATT module (six D-cell battery pack.)
OMP-PSM-2-PP	224	Stand-alone portable power supply module including 6 D-cells which can be used to provide sensor and loop excitation and instrument power for other data acquisition equipment.

Power supply modules are supplied with complete operator's manual.

Ordering Example: OM-320-PSM-2 power supply module for OM-320 datalogger and OMEGACARESM extended warranty (adds 1 year to standard 1 year warranty), \$160 + 25 = \$185.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters