

Dissolved Oxygen Meter with Real Time SD Card Data Logger

DOH-SD1
£469



- ✓ LCD with Green Light Backlighting
- ✓ Real Time SD Memory Card Data Logger (SD Card Included)
- ✓ Altitude and Salt Adjustments
- ✓ RS232/USB Interface (with Optional Cable)
- ✓ Automatic Temperature Compensation

The OMEGA® DOH-SD1 is innovative and easy to operate. What sets the DOH-SD1 apart from other dissolved oxygen meters is that it incorporates a real-time SD card data logger. The DOH-SD1 measures dissolved oxygen and has adjustments for altitude and salt. Download data from the SD card into an Excel spreadsheet. This allows the user to do further data or graphical analysis without special software. The DOH-SD1 has a wide variety of applications from water conditioning, aquariums, and fish hatcheries to food processing, educational and other laboratories.

Specifications

Display: 52 x 38 mm (2.04 x 1.5") LCD with switchable green backlight

Measurement:

Dissolved Oxygen: 0 to 20 mg/L

Air Oxygen: Reference only

Sampling Time:

Auto: 1 second to 8 hrs 59 min 59 sec

Manual: Push the data logger button once will save data one time

Memory Card: SD memory card (with optional SD card)

Display Update: @ 1 second

Data Output (RS232/USB): With optional cable/software

Operating Temperature: 0 to 50°C (32 to 122°F)

Operating Humidity: Less than 85% RH

Power: 6 "AAA" alkaline batteries (included), or 9V power adaptor (optional)

Current Draw: 14 mA DC (without SD card or back light), 49 mA (all functions)

Weight:

Meter: 489 g (1.08 lb)

Probe: 335 g (0.74 lb)

Dimensions:

Instrument: 177 L x 68 W x 45 mm D (6.96 x 2.67 x 1.77")

Probe: 28 dia x 190 mm (1.1 x 7.48")

Measurement and Range:

Dissolved Oxygen: 0 to 20.0 mg/L (liter)

Oxygen in Air: 0 to 100.0% (reference only)

Temperature: 0 to 50°C (32 to 122°F)

Resolution:

Dissolved Oxygen: 0.1 mg/L

Oxygen in Air: 0.1%

Temperature: 0.1°C (32.18°F)

Accuracy:

Dissolved Oxygen: ±0.4 mg/L

Oxygen in Air: ±0.7%

Temperature: ±0.8°C (1.5°F)

Compensation:

Automatic Temperature: 0 to 50°C (32 to 122°F)

Adjustable Salt: 0 to 50%

Elevation: 0 to 8900 meters

Oxygen Probe: Polarographic



DOH-SD1, £469.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
DOH-SD1	£469	Data logging dissolved oxygen meter with SD card
SW-U101-WIN	66	Software for data logging from meters
HC-SD	20	Replacement hard case
SC-SD	10.75	Soft case
ADAPTER-SD	13.50	AC adaptor
USB-SD	43.50	USB cable (SW-U101-WIN software required)
RS232-SD	16.75	RS232 cable (SW-U101-WIN software required)
DOE-SD1	121	Replacement dissolved oxygen probe
DOEH-SD1	4.70	Replacement dissolved oxygen probe head
DOEL-SD1	9.40	Replacement dissolved oxygen electrolyte
2GB-SD	6.70	Spare 2 GB SD memory card

Comes complete with operator's manual, probe, spare probe head, electrolyte, 2 GB SD card, hard carrying case and 6 "AAA" batteries.

Ordering Example: DOH-SD1, data logging dissolved oxygen meter with SD card and ADAPTER-SD, AC adaptor, £469 + 13.50 = **£482.50**

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters