

NEW

INDUSTRIAL pH INSTRUMENTATION & ELECTRONICS



Industrial pH Instrumentation & Electronics Mini Panel-Mount pH Controller

PHCN-201
\$120



- ✓ User-Selectable Acid or Alkaline Relay
- ✓ Simple One-Point Calibration
- ✓ Reduced Size to Facilitate Installation
- ✓ Choose from 100 to 240 V or Low Voltage 12 Vdc Models
- ✓ Practical and Convenient

PHCN-201 is a simple-to-operate pH controller specially designed for applications where space or costs are a major concern. Thanks to its compact size of only 8 x 5 cm (3 x 2"), PHCN-201 can be mounted in confined spaces and right next to tanks or vats. The low cost of the meter will also make it possible for processes that up to now were manually maintained to be controlled automatically, saving considerable time and money. Measurements are displayed in large digits on the LCD and LED lights indicate the exact status of the controller, even from a distance. PHCN-201 also incorporates a bi-directional relay. Through a simple jumper on the rear of the meter, the operator can select acid dosage, which means the relay is activated with measurements above the setpoint, or alkaline with relay closed when measuring below the setpoint. In order to adjust the setpoint from 0 to 14 pH or to calibrate meter at any point on the scale, simply turn the relevant trimmer right on the front panel. The controller is easy to use and to install. Any combination pH electrode with a BNC connector can be hooked up to the meter. The meters are available in three models to best suit your application. You can choose from the 100 to 110 V or the 220 to 240 V operated model. For those who prefer to operate at low voltage, there is also the 12 Vdc version with the transformer included in the low cost of the meter.

Specifications

Range: 0.0 to 14.0 pH
Resolution: 0.1 pH
Accuracy (@ 20°C/68°F): ±0.2 pH
Calibration:
 1 point adjustable with trimmer
Setpoint: Adjustable from 0.0 to 14.0 pH with trimmer
Relay Control: 2 amps @ 220 Vac Selectable acid or alkaline dosage
Acid: Activated when reading higher than setpoint
Alkaline: Activated when reading lower than setpoint



PHE-1411 pH electrode sold separately, \$60. Shown smaller than actual size.



Power Supply: 110/115V; 50 to 60 Hz
 External 12 Vdc (optional)
 220/240V; 50 to 60 Hz (optional)
Environment: 0 to 50°C
 (32 to 122°F); max. RH 95%

Dimensions: 79 x 49 x 95 mm (3.1 x 1.9 x 3.7")
Weight: 150 g (5.3 oz.)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| Model No. | Price | Description |
|-------------|-------|---|
| PHCN-201 | \$120 | Mini panel mount pH controller |
| PHE-7351-15 | 125 | Industrial electrode for in-line or submersion |
| PHE-1411 | 60 | Laboratory double junction, plastic body, gel-filled combination pH electrode with 1 m (3.3') cable |
| PHA-77 | 35 | Third arm electrode holder for laboratory electrodes |
| PHA-4 | 5 | 4.00 pH buffer solution 475 ml bottle |
| PHA-7 | 5 | 7.00 pH buffer solution 475 ml bottle |
| PHA-10 | 5 | 10.00 pH buffer solution 475 ml bottle |

Comes with complete operator's manual.

Add "-12VDC" or "-240VAC" for optional power requirements, no additional charge.

Ordering Example: PHCN-201, pH controller, PHE-7351-15, pH electrode, PHA-4, 4.01 buffer solution, PHA-7, 7.01 buffer solution, \$120 + 5 + 5 = \$130.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters