

# IN-LINE FLOWMETERS

## FL-500WW Series



Optional †

- ✓ Direct Flow Indication
- ✓ PVC Body and End Fittings
- ✓ Titanium Shaft and Spring
- ✓ Easily Mounted in Any Pipe Orientation

### Typical Applications

- ✓ Aluminum Sulfate (Alum)—Clarification
- ✓ Chlorinated Water—Disinfection
- ✓ Ferric Chloride—Clarification
- ✓ Potassium Permanganate—Disinfection

- ✓ Sodium Bisulfite—Disinfection
- ✓ Sodium Hypochlorite (Bleach)—Disinfection
- ✓ Sodium Hydroxide—Neutralization
- ✓ Sulfur Dioxide (in Water)—Dechlorination
- ✓ Chlorine Dioxide—Disinfection

The FL-500WW Series provides flow rate indication for 1 to 5% dilute aqueous chemical solutions used in the treatment of water and wastewater.

**Dimensions:** 177.8 mm (7") long  
**FL-505 through FL-515:**  
 50.8 mm (2") Dia.  
**FL-520 through FL-550:**  
 76.2 mm (3") Dia.



FL-505WW, shown smaller than actual size.

**To Order Visit [omega.com/fl500ww](http://omega.com/fl500ww) for Pricing and Details**

Model No.	Female NPT End Fittings	Dual Scales	
		GPM	LPM
FL-505WW	1	0.5 to 5	2 to 20
FL-510WW	1	1 to 10	4 to 38
FL-515WW	1	1.5 to 15	6 to 55
FL-520WW	1.5	2 to 20	8 to 75
FL-530WW	1.5	3 to 30	11 to 110
FL-540WW	1.5	4 to 40	15 to 150
FL-550WW	1.5	5 to 50	20 to 200

### SPECIFICATIONS

Fluid Temperature		Max Liquid Pressure	
°C	°F	psig	bar
21	70	200	13.79
38	100	100	6.90
52	125	75	5.17
65	150	50	3.45

### Accessory Switch Kits (Field Installable)

Model No.	For Sizes
FL-500-S1	FL-505, FL-510, FL-515
FL-500-S2	FL-520, FL-530, FL-550

Switch ratings: 8 W, 100 Vdc/120 Vac.  
 Comes complete with operator's manual.

† For NIST traceable certificate add suffix “-NIST” to model number for additional cost.

**Ordering Examples:** FL-515WW, 1" flowmeter, 1.5 to 15 GPM (6 to 55 LPM).

FL-530WW, 1.5" flowmeter, 3 to 30 GPM (11 to 110 LPM).

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

**www.omega.co.uk**



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters