




INDUSTRIAL pH INSTRUMENTATION & ELECTRODES

Industrial pH/ORP Controller/Recorders With Integral 30 Day Chart Recorder



PHCN-45, \$1314, shown smaller than actual size.

PHCN-45
Starts at
\$1314



- ✓ Combines pH Measurement, Recording, and Controlling in One Unit
- ✓ High Visibility 150 mm (6") Mirrored Analog Display
- ✓ Built-in 30 Day Chart Recorder
- ✓ High and Low Setpoints and Alarms
- ✓ Time Delay Safety Feature
- ✓ On/Off Control

PHCN-45

The PHCN-45 combines pH/ORP measurement, recording and control in a single compact unit. pH and millivolt readings are displayed on a 6" mirrored meter and the built-in chart recorder provides a 30 day record. In the standard mode, accuracy is ± 0.1 pH and ± 10 mV. If increased accuracy is required, a 10x scale expansion is provided. Easy to use front panel controls can set both the high and low limits for control to within 0.1 pH and to activate a visual alarm when limits are

exceeded. If desired, an adjustable Time Delay Safety Feature will shut off power to the output if the pH does not return to the control point within set time (0 to 30 minutes). This can prevent over addition of neutralizing chemicals due to probe or meter malfunction. A pulsed 5 Vdc alarm output is available to drive a dc solid state relay to indicate this condition.

Specifications

Input Parameters: pH, ORP
Display: 150 mm (6") analog meter and recorder
Inputs: PHCN-45, 47: 1; PHCN-48: 2
Standard Ranges: 0 to 14 pH; ± 900 mV
Expanded Ranges: 1.4 pH; ± 90 mV
Accuracy, pH: ± 0.1 pH, ± 0.01 pH expanded
Accuracy, ORP: ± 10 mV, ± 1 mV expanded
Temperature: 0 to 100°C, manual
Output Control: Two separate 4 A SSRs
Time Delay: 0 to 30 min




Recorder: 30 day chart
Power Consumption: 55 W @ 115/230V (maximum)
Alarm Signal Output: 3.5V p-p (Squarewave), 20mA
Housing:
PHCN-45: Benchtop
PHCN-47/48: NEMA 12 wall mount
Dimensions:
PHCN-45: 203 H x 356 W x 279 mm D (8 x 14 x 11")
PHCN-47/48: 305 H x 356 W x 152 mm D (12 x 14 x 6")
Weight:
PHCN-45: 10.9 kg (24 lb)
PHCN-47/48: 9 kg (16 lb)



PHCN-48
\$1674

PHCN-48

The PHCN-48 is similar to the PHCN-47 with the addition of a second electrode input that allows the user to connect one electrode to the meter/controller and the other to the recorder so that real-time monitoring of the control system is possible. In typical applications, the first electrode is placed in the input water flow where it senses pH and activates the control system. The second electrode, located downstream, drives the recorder to provide a continuous record of the pH of the effluent from the control system.



PHCN-48, \$1674, shown smaller than actual size.

PHCN-47
\$1554

PHCN-47

The PHCN-47 is a single electrode input model that combines the same functions as the PHCN-45 in a NEMA 12 type cabinet that may be used in a harsh environment.



PHCN-47, \$1554, shown smaller than actual size.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
PHCN-45	\$1314	Benchtop pH controller/recorder
PHCN-47	1554	Wall mounted pH controller/recorder
PHCN-48	1674	Wall mounted pH controller/recorder with separate inputs for control and recording

Accessories

Model No.	Price	Description
SL-652	\$11	Chart paper, 40 division
PHE-5311-10	103	In-line disposable electrode
PHE-6351-10	114	Submersible electrode
PHCN-45-CHART-0-14	11	0 to 14 scale paper

Comes complete with operator's manual.

Electrodes sold separately.

Ordering Examples: PHCN-47, wall-mounted pH controller/recorder, PHCN-45-CHART-0-14, 0 to 14 range paper, and PHE-6351-10 submersible electrode, \$1554 + 11 + 114 = \$1679.

PHCN-45 bench top pH controller/recorder, PHCN-45-CHART-0-14, 0 to 14 range paper, and PHE-6351-10 submersible electrode, \$1314 + 11 + 114 = \$1439.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters