

DIGITAL FLOW TRANSMITTERS

FP1521
Starts at
\$780



Standard Features

- ✓ Easy Commissioning Thanks to Multi-Language, Menu-Guided Operation
- ✓ Individual Adjustment of All Measuring Parameters
- ✓ Compact Design
- ✓ Large, 15 mm, Clear LCD
- ✓ Measurements from 0.3 to 30 fps
- ✓ Volumetric Flow Measurement with 2 Optional Totalizers
- ✓ Easy Processing by 4 to 20 mA Output Signal, Pulse Output, and Optional Alarm Relay
- ✓ Wetted Parts Made of PVDF/Ceramic with FPM/EPDM Gaskets

Applications

- ✓ Flow Measurement
- ✓ Industrial Wastewater Treatment
- ✓ Water Treatment and Process Technology
- ✓ Cooling Water Monitoring

Batch Control

- ✓ Chemical Dosing and Filling Systems



FP1521, \$780, shown larger than actual size, with FP1110-PO-A, \$190.

DESIGN

The compact FP1520 Series paddlewheel flow transmitter is designed for use in aggressive, solid-free liquids.








The measuring principle is based on local velocity measurement. The transmitter produces a 4 to 20 mA standard signal proportional to the flow and provides a freely adjustable pulse output. Both signals can easily be transmitted and processed. The display and operating elements allow customized adjustment of all measuring parameters.

A specially designed fitting system ensures simple installation of the devices into all pipes.

- 4 to 20 mA, 2-wire
- Paddlewheel hall sensor, 1:100 measurement dynamic (max 30 fps)
- Menu-guided operation:
 - Multi-language
 - Choice of engineering units
 - Customized measuring ranges
- Volumetric flow measurement with 2 optional totalizers:
 - Display, memory, and individual reset functions
- On-site alarm function:
 - Freely programmable limit values with engineering units, owing to two optional relays




ACCURACY The accuracy of every FP150 is tested and calibrated on a flow test bench over its entire measuring range.



INSTALLATION


OMEGA's specially designed fitting system allows for easy installation of flow transmitters into pipes (see instructions in the diagram at right). This will ensure accurate measurement. Pressure and temperature tolerances must also be observed, depending on the selected fitting material. (Please refer to the operator's manual for flow transmitter FP1520.)



OPERATION/ COMMISSIONING

The device can be calibrated using the K-factor or via the Teach-In function. Customized adjustments of the measuring range, engineering units, resolution of pulse output and totalizers can be carried out on site with the menu-supported multi-lingual display.

Pressure-Temperature Diagram



SELECTION EXAMPLE

Select the appropriate pipe size using the diagram below.


Example:

Specification of nominal flow: 50 GPM


Ideal flow velocity: 5 to 10 fps

For these specifications, the diagram indicates a pipe size of 2".


Selection of Nominal Size



Cable Gland (Units with Relays)



Cable Plug Version (Units Without Relays)



F

SPECIFICATIONS

Pipe Diameter: ½ to 8"

Ambient Temperature: 0 to 60°C
(32 to 140°F)

Fluid Temperature: 0 to 80°C
(32 to 176°F), version with Hall sensor;
0 to 120°C (32 to 248°F), optional
version with coil

Storage Temperature:
-10 to 80°C (14 to 176°F)

Fluid Pressure: Max 10 bar (145 psi),
depending on fluid temperature and
installation fitting

Enclosure: NEMA 12 (IP65)

Measuring Range:

**Freely Programmable (with Units)
with Hall Sensor:**

0.1 to 10 m/s (0.3 to 30 fps)

With Coil: 0.3 to 10 m/s (1.0 to 30 fps)

Accuracy: <1% within 1.6 to 30 fps;
<5% within 0.3 to 1.5 fps

Repeatability: 0.4% of measured value

Voltage Supply: 12 to 30 Vdc

Output Signal : 4 to 20 mA

Load: Max 900 Ω at 30 V

Pulse Output: Freely programmable;
open-collector NPN and PNP; 0 to 30 V,
100 mA; protected

Display: 15 x 60 mm (0.6 x 2.4"),
8-digit, alphanumeric LCD;
15 segments, 9 mm H (0.35")

Relay Output:

Freely programmable, 3 A, 230 V

Sensor Fitting: PVDF

Paddlewheel: PVDF

Axis and Bearing: Ceramic

O-Rings:

Standard: FPM

Optional: EPDM

Housing: Polycarbonate

Front Plate Foil: Polyester



FP1521, \$780,
shown with
FP1110-PO-A,
\$190, smaller than
actual size.



FP1521, \$780,
sensor photo

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No.	Price	Description
FP1521	\$780	Paddlewheel sensor, hall type, FPM O-rings, ½ to 4" pipes, no totalizer, no relays
FP1522	780	Paddlewheel sensor, coil type, FPM O-rings, ½ to 4" pipes, no totalizer, no relays
FP1523	780	Paddlewheel sensor, hall type, FPM O-rings, 5 to 8" pipes, no totalizer, no relays

Comes with complete operator's manual

To add 2 relays (3 amp up to 220 Vac), add suffix "-R" to the model number and add \$115 to the price. To add 2 independently resettable totalizers, add suffix "-T" to the model number and add \$140 to the price. To order EPDM O-rings in place of the standard FPM O-rings, add suffix "-EPDM" to the model number, no additional charge.

Ordering Examples: FP1521-R, paddlewheel sensor with 2 relays, \$780 + 115 = \$895. FP1522, transmitter, FP1005-A, PVC fitting, \$780 + 94 = \$874.

Accessories

Model No.	Price	Description
PSU-93	\$40	Wall socket plug-in transformer, 115 Vac in, 24 Vdc out on screw terminals
CM-0902	495	Reference Book: Corrosion Resistance Tables



Required Transmitter Fittings

Pipe Size	PVC Schedule 80		PVDF		Polypropylene		Stainless Steel	
	Model No.	Price	Model No.	Price	Model No.	Price	Model No.	Price
½"	FP1005-A	\$96	FP1105-A	\$279	FP1105-PO-A	\$167	N/A	—
¾"	FP1007-A	105	FP1107-A	318	FP1107-PO-A	176	FP1007-SS-A	\$295
1"	FP1010-A	106	FP1110-A	379	FP1110-PO-A	202	FP1010-SS-A	295
1¼"	FP1012-A	138	N/A	—	FP1112-PO-A	227	FP1012-SS-A	312
1½"	FP1015-A	151	N/A	—	FP1115-PO-A	268	FP1015-SS	312
2"	FP1020-A	174	FP1120-A	797	FP1120-PO-A	343	FP1020-SS	312
2½"	FP1025	171	N/A	—	N/A	—	FP1025-SS	395
3"	FP1030	190	N/A	—	N/A	—	FP1030-SS	395
4"	FP1040	195	N/A	—	N/A	—	FP1040-SS	395
6"	FP1060	223	N/A	—	N/A	—	FP1060-SS	395
8"	FP1080	376	N/A	—	N/A	—	FP1080-SS	395

Note: PVC, PVDF and polypropylene fittings up to and including 2" line size are tees with union nuts and socket-weld connections; PVC fittings from 2½" through 8" are saddle fittings. SS fittings up to and including 1¼" line size are FNPT threaded; SS fittings from 1½" through 8" line size are weld-on fittings.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters