

# ADJUSTABLE DEPTH BRASS FLOW SENSORS

Doesn't Need  
Special Installation  
Fittings!

FP-6000 Series  
Starts at

**\$479**



- ✓ One Sensor for Lines 38 to 914 mm (1½ to 36")
- ✓ No Special Fitting Needed
- ✓ Low Cost

When you want it all in one flow sensor, you want the FP-6000 sensor. Accuracy...durability versatility...easy installation... low cost—the FP-6000 gives you all this.

The FP-6000 accurately measures a wide variety of fluids with flowrates as low as 1.6 feet per second up to 20 feet per second. It generates a sine-wave frequency output linearly proportional to flowrate with ±0.2 fps accuracy.

The FP-6000 is versatile, adjusting to various pipe sizes. There is no need to buy a different sensor for every change in pipe size. You can position the FP-6000 to give you accurate readings in any size pipe (1½ to 36"), permitting tremendous cost savings.

No special fittings are required. A standard 1½" threadolet or saddle fitting is all you need.

Made of rugged brass, the FP-6000 can handle harsh environments. The output signal can be sent up to 30 m (100') without amplification. Each FP-6000 sensor comes with a 7.5 m (25') cable and all necessary mounting hardware.

## SPECIFICATIONS

**Output Signal:** Sine wave, 80 mV p-p/fps

**Output Frequency:** 11 Hz/fps

**Source Impedance:** 10,000 Ω

**Flow Rate Range:** 1.6 to 20 feet per second (fps)



**Linearity:** ±1% of full range

**Repeatability:** ±0.5% of full range

**Maximum Operating Pressure:** 225 psi

**Maximum Operating Temperature:** 100°C (212°F)

**Max Viscosity:** 1 centipoise (water); up to 5 cp above 5 fps velocity



FP-6000, \$479, brass flow sensor, shown smaller than actual size.

## MATERIALS

### Sensor

**Rotor:** CD4MCu Stainless Steel

**Rotor Shaft:** Tungsten Carbide Steel

**Transducer Body:** C 36000 Brass

**Bearing:** Carbon/graphite filled fluoroplastic (Fluoroloy B)

**Fitting Housing and Cover:** Brass

**Seal:** FKM O-Ring

**Shipping Weight:** 2.7 kg (6 lb)

**Dimensions:** From flange to rotor pin, 151 mm (5.94"), overall cable type twisted pair with foil shield

**Connection:** 1½ NPT or 1.5" ISO

**Cable Length:** 7.5 m (25')

**MOST POPULAR MODELS HIGHLIGHTED!**

Compatible Meters:  
DPF700 (page M-5),  
DPF70 (page M-22)  
with FLSC-AMP, FP90 (page F-31),  
FPM-5500 (page F-43),  
FPM-9020A (page F-42).

## To Order (Specify Model Number)

Model No.	Price	Description
FP-6000	\$479	Adjustable brass flow sensor, 1.5 NPT thread
FP-6001	479	Adjustable brass flow sensor, 1.5" ISO thread
FP-6002	741	Adjustable brass hot-tap flow sensor, 1.5 NPT thread
FP-6003	741	Adjustable brass hot-tap flow sensor, 1.5" ISO thread
FP-3-1500-302	411	Hot-tap installation tool
FP-52509-1	48	Complete replacement 316 SS rotor/paddlewheel kit
FP-52509-2	61	Complete replacement Tungsten Carbide rotor/paddlewheel kit

Comes complete with operator's manual.

**Ordering Examples:** FP-6000, adjustable brass paddlewheel flow sensor, 1.5 NPT thread, \$479. FP-6003, adjustable brass hot-tap flow sensor, 1.5" ISO thread, \$741.

Recommended Reference Book: Flow Measurement for Engineers and Scientists, MS-0918, \$240. See Section Y for Additional Books.



# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters