

pH OR ORP CONTROLLER AND PUMP

PHP-701
Starts at

£ **442**




See next page
for accessories

- ✓ pH or ORP Controller and Dosing Pump in One Compact Unit
- ✓ ± 0.01 pH / ± 5 mV Accuracy with Unbeatable Performance
- ✓ Isolated 4 to 20 mA Recorder Output
- ✓ Proportional Dosing Slows the Pump Down When the Measured pH or ORP Level Approaches the Set Value Which Ensures Precise Dosage and Avoids Costly Waste of Chemicals Due to Overdosage
- ✓ Alarm Contact is Activated Whenever the pH or ORP Value Varies by More than 2 pH or 200 mV Units from the Setpoint
- ✓ Auxiliary Contacts Allow the User to Attach a Mixer or Priming Pump that is Activated only When the Pump is Dosing
- ✓ PVDF, FKM and PTFE Materials Are Used for All Parts that Come into Contact with Liquid

TWO ADVANCED INSTRUMENTS IN ONE

The PHP-700 Series pumps combine the powerful PHP-600 series dosing pumps with the state-of-the-art controllers. These unique products were developed for measuring and controlling pH or ORP and the regulated dosing of various chemicals. The latest innovation eliminates the need for multiple instruments by combining two instruments into one. No more complicated installations, wiring, and compatibility problems. This compact system features accurate



PHP-701, £442 and PHE-1411, £42, electrode (sold separately) shown smaller than actual size. See omega.co.uk for details.

regulation, proportional dosing, alarm and recorder signals and much more all in one unit.

EASY INSTALLATION

Designed with mounting holes in the rugged base, the PHP-700 Series pump/controllers are simple to install. There is no need for any additional hardware. All of the controls and pump assemblies are conveniently located on the front of the unit. If the operator must access the pump head or control panel for any reason, there is no need to dismount the unit.

RUGGED CONSTRUCTION

The PHP-700 Series pump/controllers are housed in rugged, fiber-reinforced polypropylene casings. They are IP65 rated, preventing ingress of liquids. The material used for the housing resists corrosion caused by most chemicals, protecting the unit from hazardous spills and splashes.

SUPERIOR MATERIALS

The PHP-700 Series pumps use PVDF, FKM and PTFE materials for all components in contact with the

chemicals being dosed. These materials have properties that enable them to resist even the most corrosive chemicals in the industry. The choice of material makes the pump more versatile, allowing it to be used to handle a wider variety of reagents.

SIMPLE PUMP ACTION

A positive displacement solenoid with few moving parts makes PHP-700 Series pumps more reliable than motor driven pumps. With no rotating parts, gears or cams, part wear and oiling associated with motor driven pumps is eliminated, drastically reducing any chance of mechanical failure.

FLOW, LEVEL AND ENVIRONMENTAL

PROPORTIONAL DOSING

The PHP-700 Series controller/pump strokes at full capacity when the measured value deviates by more than 1.5 pH or 150 mV from the set value. A proportional control slows down the stroke rate as the measured value approaches the user-selectable value, avoiding over-dosage of chemicals. This feature makes the pump's dosing more accurate, saves chemicals and eliminates unnecessary and costly corrections of your processes, especially with slow reacting chemicals.

ISOLATED RECORDER OUTPUT

To enhance troubleshooting and provide the user with the ability to record data while monitoring, the PHP-700 Series controller/pumps provide for a recorder output. By simply attaching a recorder to the instrument's 4 to 20 mA output contacts, conveniently located on the front panel, you can obtain a hard copy of the results on demand.

ALARM OUTPUT

When monitoring and controlling pH and ORP levels in a process, it is very important that any potential problem will not go unattended. The units incorporate an alarm system that will alert the user if the reaction is not within certain guidelines. The alarm of the PHP-700 Series will be activated if the measured pH value is 2 pH units lower than the setpoint (if dosing acid, this indicates overdosage, a common symptom

Maximum Capacity	
Pressure	Flow
bar	LPH
1.0	11.7
2.0	10.1
4.0	7.8

of siphoning). The alarm will also activate if the value is 2 pH higher than the setpoint (if dosing acid, this is an indication of insufficient dosage, a common symptom of the lack of reagent). The alarm will activate if the mV value is 200 mV lower than the setpoint (if dosing reducing chemicals, this indicates overdosage). The alarm will also activate if the value is 200 mV higher than the setpoint (if dosing reducing chemicals, this is an indication of lack of reagent).

AUXILIARY DOSING CONTACTS

The auxiliary dosing contacts of the units are closed whenever the pump is dosing. This solution offers considerable advantages, especially for small plants, where these pumps need to be the only equipment left running. This will spare other equipment such as mixers, priming pumps etc. With this feature activated, a mixer can be automatically started, when the pump is dosing.



SPECIFICATIONS

Power Supply:

110/115V 50/60 Hz ±15% (40 W)
220/240V 50/60 Hz ±15% (40 W)
(optional)

Range: 0.00 to 14.00 pH;
0 to ±999 mV

Resolution: 0.01 pH; 1 mV

Accuracy: ±0.01 pH; ±5 mV

Input: High impedance 1012 BNC Connector

Dosage: Proportional; acid or base; oxidising or reducing.
User selectable

Dosing Contact: Isolated, 2A, Max 240V, resistive load, 1,000,000 strokes

Alarm Contact: Isolated, 2A, Max 240V, resistive load, 1,000,000 strokes

Calibration:

Offset: ±1 pH by offset trimmer

Slope: 85 to 115% by slope trimmer

Recorder Output: 4 to 20 mA, isolated

Environment: 0 to 50°C

Dimensions: 181 L x 221 W x 142 mm H

Weight: 5 kg


 **MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)

Model No.	Price	Description
PHP-701	£442	pH controller and metering pump, 110 Vac powered
PHP-702	442	ORP controller and metering pump, 100 Vac powered
PHE-7351-15	90	Industrial electrode for in-line or submersion
PHA-4	3.40	4.01 pH buffer solution 475 ml bottle
PHA-7	3.40	7.01 pH buffer solution 475 ml bottle
PHA-10	3.40	10.01 pH buffer solution 475 ml bottle
ORE-6510	96	ORP submersible electrode
PHEH-65-10	33	Required mounting assembly for ORE-6510

Accessories (see page 541 for additional information)

AVAILABLE FOR FAST DELIVERY!

Model No.	Price	Description
PHP-600-PHK	£47.00	PVDF pumphead, PTFE coated O-ring and 6 screws and washers
PHP-600-DVA	16.75	Spare discharge valve assembly, complete with a FKM O-ring, glass valve ball, the valve spacer and seat, head nipple and the tube nut to secure the assembled parts
PHP-600-SVA	16.75	Spare suction valve assembly, complete with a FKM O-ring, glass valve ball, the valve spacer and seat, head nipple and the tube nut to secure the assembled parts
PHP-600-IVA	15.50	Injection valve assembly, complete with and injection nipple, PTFE coated spring, glass valve ball and a valve assembly
PHP-600-FVA	13.50	Foot valve assembly contains a filter with a filter holder, and a valve assembly
PHP-600-CW	16.75	4 x ceramic weight
CM-0490	117.00	Reference Book: Chemical Process Equipment 

Comes complete with discharge and suction valves and operator's manual.

Add "-220VAC" to model number for 220/240V operation, no additional charge.

Ordering Example: PHP-701-220VAC, controller and chemical metering pump, 230 Vac powered, PHE-7351-15, pH electrode, PHA-4, 4.01 pH buffer, PHA-7, 7.01 pH buffer, £442 + 90 + 3.40 + 3.40 = **£538.80**.



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters