

OMEGA-FLO® 3-WAY SOLENOID VALVES FOR PNEUMATICS

1/4 NPT

SV-1601A
\$197





- ✓ Ideal for Air Cylinders and Actuators
- ✓ Manual Override Standard
- ✓ 120 Vac Standard (DC Optional)
- ✓ Low Power Consumption

The SV-1600A Series 3-way solenoid valve is an internally piloted poppet valve featuring an epoxy-encapsulated coil, Buna seals, low power consumption, and a high cycle rate. It also has a high-quality plastic body with pressed-in threaded bushings and a built-in sintered bronze silencer in the relief port. Manual override is standard. Temperature range is -10 to 60°C (14 to 140°F). This valve is ideal for compressed air to actuate medium-sized cylinders and actuators. Electrical connection is by conduit plug.

SPECIFICATIONS

Mounting Position: Any (relief port R with built-in sintered bronze silencer is in the base and must not be covered)
Max Ambient Temp: 54°C (130°F)
Voltage Tolerance: ±10%



Power Consumption in Warm State:

AC: 3.5 VA/2 W
 DC: 2 W

Opening Time (ms): Approx. 50

Closing Time (ms): Approx. 30

Cycling Rate: Approx. 1000 cpm

Duty Cycle: Continuous (100%)

FM Approvals: Non-incendiary for hazardous locations Class I, Div. 2, Group A, B, C, D; Class II, Div. 2, Group F, G; Class III, Div. 1 and 2; Operating Temperature T4A

SV-1601A, \$197, shown larger than actual size.



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)								
Model No.	Price	Port Connection (NPT)	Cv	Pressure Range ¹ (psi)	Orifice Diameter	Valve Operation	Weight kg (lb)	Body Material
SV-1601A	\$197	1/4	0.97	15 to 140	1/4"	Normally closed	0.3 (0.66)	Plastic

¹A pressure differential of at least 15 psi is required to ensure operation.

Comes complete with operator's manual.

Ordering Example: SV-1601A, plastic valve, 0.97 Cv, normally closed operation, \$197.

Accessory

Model No.	Price	Description
ME-1849	\$110	Reference Book: Fluid Machinery

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters