

HOT WIRE ANEMOMETER WITH REAL TIME DATA LOGGER



HHF2005HW
£432

- ✓ Real Time Data Logger Records Year, Month, Date, Hour, Minute and Second—Up to 16,000 Records
- ✓ Hot Wire Technology for High Precision, Low Velocity Air Measurements
- ✓ RS232 Serial Interface and Software Available
- ✓ Battery Powered Meter Includes Hard Carrying Case for Easy Portability
- ✓ Slim Telescopic Probe is Ideal For Grilles and Diffusers
- ✓ Jumbo LCD With Multiple Displays Can be Adjusted for Brightness
- ✓ Adjustable Sampling Time, Zero Adjust and Data Hold Features
- ✓ Accepts Type J or K Thermocouple

The HHF2005HW hot wire anemometer with real time data logger has multiple features and an RS232 computer interface that make it suitable to use in such applications as environmental testing, balancing of fans/motors/blowers, air conveyors, clean rooms and flow hoods. What sets the HHF2005HW apart from other hot wire anemometers is that it incorporates a real-time data logger that can store up to 16,000 entries. The HHF2005HW measures velocity, and air temperature, and has an input probe socket that accepts a Type J or K thermocouple that can be used as a highly accurate thermometer. By entering the area into the instrument and



HHF2005HW, £432, shown smaller than actual size.

measuring the velocity, the HHF2005HW can even determine the volume of air flow. The integrated hot wire and standard thermistors provide fast and accurate readings—even at low

velocities. For added convenience, the HHF2005HW is battery powered, has auto power off and low battery warning features. A hard carrying case is included, to make portability simple.



Hard carrying case, operators manual, 1 CR2032 battery and 4 "AA" batteries included.



SPECIFICATIONS

Display Units: m/s, km/h, mile/h, knot, ft/min, CMM, CFM, °C, °F

Operating Temperature: 0 to 50°C (32 to 122°F)

Max Humidity: Less than 80% relative humidity (non-condensing)

Sampling Time: 2 sec to 8 hours, 59 min, 59 sec

Power Supply: 4 "AA" and 1 CR2032 batteries (included)

Current: Approx 21.5 mA DC (70 mA DC with hot wire probe)

Weight: Approx 515 g (1.13 lb)

Dimensions:

Instrument: 203 x 76 x 38 mm (8.0 x 3.0 x 1.5")

Telescopic Probe: 12 mm (0.5") dia, 280 to 940 mm (11.0 to 37.0") length

LCD Display: 58 x 34 mm (2.3 x 1.3")

Measurement	Range	Resolution	Accuracy
m/s	0.2 to 20 m/s	0.1 m/s	± (5% + 1sd) reading or ± (10% + 1sd) full scale
km/hr	0.7 to 72 km/hr	0.1 km/hr	
mile/hr	0.5 to 44.7 mile/hr	0.1 mile/hr	
knot	0.4 to 38.8 knot	0.1 knots	
ft/min	40-3940 ft/min	1 ft/min	
Air temp (°C)	0 to 50°C	0.1°C	± 0.8°C
Air temp (°F)	32 to 122°F	0.1°F	± 1.5°F
Thermometer (Type J thermocouple)	-100.0 to 1100°C	0.1°C	± (0.2% + 0.5°C)
	-50.1 to -100°C		± (0.2% + 1°C)
	-58.0 to 2012°F	0.1°F	± (0.2% + 1°F)
	-58.1 to -148°F		± (0.2% + 1.8°F)
Thermometer (Type K thermocouple)	-50.0 to 1300°C	0.1°C	± (0.2% + 0.5°C)
	-50.1 to -100°C		± (0.2% + 1°C)
	-58.0 to 2372°F	0.1°F	± (0.2% + 1°F)
	-58.1 to -148°F		± (0.2% + 1.8°F)

Measurement	Range	Resolution	Area
CMM	0 to 36,000 CMM	0.001-1 CMM	0.001 to 30.0 m ²
CFM	0 to 1,271,200 CFM	0.01-100 CFM	0.01 to 322.91 ft ²

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
HHF2005HW	£432	Hot wire anemometer with data logger
HHF2005HW-RP	121	Replacement probe for HHF2005HW
SWCABLE	77	Data logging software for the HHF2005 series with cables
CAL-3-FLOW	151	Traceable 4-point calibration certificate with test results
OP-6	228	Reference Book: Fundamentals of Temperature, Pressure and Air Flow Measurement

Comes complete with sensor, 1 CR2032 battery, 4 "AA" batteries, hard carrying case and operator's manual.

Ordering Example: HHF2005HW, hot wire anemometer with data logger, £432.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters