

PURE WATER, CORROSIVE SOLUTION & HIGH TEMPERATURE GAS APPLICATIONS

NWHMTSS, NWHIS, NWHOIS & GCHIS Series

- ✓ Screw Plug or Flanged Heater Design
- ✓ 3 - 14" Type 304 Stainless Steel Pipe Body, 150 Lb Construction
- ✓ 2 - 200 kW
- ✓ 120, 240 and 480V, 1 & 3 Phase
- ✓ General Purpose, Moisture Resistant/Explosion Resistant, Explosion Resistant or Moisture Resistant Terminal Enclosure
- ✓ 0.475" Dia. Stainless Steel or INCOLOY Sheath Elements (15 - 50 W/in²)
- ✓ With & Without Thermostat
- ✓ UL, CSA and Other Third Party Approval, Listing or Certification Available on Many Models

APPLICATIONS

Pure Water:

Heating of demineralized or de-ionized water that is highly aggressive to mild steel.

Mildly Corrosive Solutions:

Heat mildly corrosive solutions (pH5 to pH9) using stainless elements and a passivated stainless pipe body.

Highly Corrosive Solutions and Oils:

Low watt density INCOLOY sheath elements coupled with a passivated Stainless Steel pipe body provides long service life when heating highly corrosive solutions and sulfur laden oils.

Steam Superheating: Increase the enthalpy and quality of steam. Smaller units can be used to make up line losses in steam generating and distribution systems.

High Temperature Gas:

INCOLOY elements and a Stainless Steel vessel enhance safe operation to nearly 1400°F outlet gas temperature in air, gas or steam superheating applications.

FEATURES

Terminal Enclosures: Standard stock heater terminal enclosure E1 General Purpose. Moisture Resistant/Explosion Resistant E2, Explosion Resistant E3 or Moisture Resistant E4 Enclosures are available as assembly stock.

Elements: Sturdy 0.475" Dia. Stainless Steel or INCOLOY sheath elements provide superior strength and rigidity. OMEGALUX elements utilize high quality resistance wire for coil construction. The coil is surrounded with high purity magnesium oxide which is compacted to a dense solid to ensure high thermal conductivity and dielectric strength.

Corrosion Resistance: NWHMTSS, NWHIS and NWHOIS pipe bodies and all Stainless Steel heating elements are passivated to provide additional resistance to corrosion.

Flanges: Type 304 Stainless Steel flanges are standard on 3" and larger circulation heaters. Flange dimensions conform to ANSI B16.5 standards. Series NWHMTSS heaters utilize a Stainless Steel screw plug.

Vessels: Pipe body and nozzles are type 304 ASTM A312 ERW Stainless Steel pipe. The end disks are type 304 ASTM A240 Stainless Steel plate. Provided with thermal insulation and painted sheet metal jacket.

Baffle Assemblies: Internal baffle assemblies are provided for model GCHISB-18 heaters to increase the velocity of the air, gas or steam as it passes through the vessel. Increasing the velocity of the gas helps reduce the temperature of the element sheaths and the vessel walls in critical applications.

Wiring: Wiring terminals are spaced to provide proper arcing and creepage clearances per the NEC. Termination insulators provide electrical isolation between the terminals and the grounded metal sheath to enhance personnel safety and equipment service life. Heavy duty jumper straps and other terminal parts assure tight connections and an extra margin of current carrying capacity.



Controls: All stock and assembly stock heaters, Series MTSS, 03 and 06, come equipped with mechanical AR thermostats. These thermostats are suitable for most applications. Explosion-resistant and liquid-tight thermostats are provided on E2/E3 and E4 units, respectively. Individual product pages list other types of thermostats and controls available for each heater. For heaters listed without controls, refer to the Overview on Mechanical and Electrical Control Options in this section.

Precision Temperature Control and Control Panels: For larger kW heaters and precise control of gas temperatures in high temperature applications, OMEGALUX recommends the use of thermocouple sensors, electronic PID temperature controls and SCR power panels for circulation heater applications. The use of electronic and SCR controls will minimize overshoot and reduce the possibility of heater damage from overtemperature operation. Integral or remote mounted control panels with electronic controls and solid state (SCR) or contactor power controllers can be provided using virtually any combination of control devices. Consult the Controls section for details.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters