

OMEGA-FLO® 2-WAY HIGH PRESSURE SOLENOID VALVES

1/2 to 2 NPT

SV-501
Starts at
\$192



SV-501, \$192, shown larger than actual size.

- ✓ For Gases or Liquids
- ✓ Temperatures to 99°C (210°F)
- ✓ 120 Vac Standard (DC Optional)

The SV-500 Series comprises 2-way, normally closed, internally piloted piston solenoid valves. These valves have an epoxy-encapsulated coil, a brass body, PTFE sealing material for the main seat, Viton® O-rings and core seals, and a temperature range of 0 to 100°C (32 to 212°F). SV-500 Series valves are ideal for neutral media such as compressed air, hot air, water, and oxygen, and for use in breweries, fire prevention systems, water supply, and air conditioning installations. Electrical connection is by conduit plug.

SPECIFICATIONS

Mounting Position:

Any (preferably with solenoid system upright)

Max Ambient Temp: 54°C (130°F)

Voltage Tolerance: ±10%

Power Consumption in Warm State:

AC: 21 VA (inrush); 12 VA/8 W (hold)

DC: 8 W

Response Times

Orifice Size	Opening Time (ms)	Closing Time (ms)
7/16"	20 to 40	100 to 250
3/4", 1"	100 to 400	300 to 1500
1 1/4", 1 1/2"	100 to 700	600 to 1500
2"	500 to 1200	1500 to 5000

Response times are measured at outlet A on energizing/de-energizing until attainment of pressure rise to 90%/pressure drop to 10% at working pressure of 85 psi.

Cycling Rate: Up to 250 cpm with lubrication

Duty Cycle: Continuous (100%)

Options (no additional charge)

Ordering Suffix	Description
-24VDC	24 Vdc operation
-12VDC	12 Vdc operation
-240VAC	240 Vac operation

Options not available on all sizes.

MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number) Normally Closed Valve

Model No.	Price	Port Connection (NPT)	Cv	Pressure Range (psi)				Orifice Diameter	Weight kg (lb)
				Water		Air			
				AC	DC	AC	DC		
SV-501	\$192	1/2	2.4	14.5 to 362	14.5 to 362	14.5 to 362	14.5 to 362	7/16"	0.6 (1.3)
SV-502	224	3/4	5.8	14.5 to 362	14.5 to 362	14.5 to 362	14.5 to 362	3/4"	1.2 (2.7)
SV-503	353	1	11.7	14.5 to 362	14.5 to 362	14.5 to 362	14.5 to 362	1"	1.7 (3.8)
SV-504*	401	1 1/4	21	14.5 to 362	14.5 to 232	14.5 to 362	14.5 to 232	1 1/4"	2.9 (6.3)
SV-505*	454	1 1/2	21	14.5 to 362	14.5 to 232	14.5 to 362	14.5 to 232	1 1/2"	3.3 (7.3)
SV-506*	699	2	42	14.5 to 362	14.5 to 232	14.5 to 362	14.5 to 232	2"	5.8 (12.8)

Comes with complete operator's manual.

* Note: Only the SV-501, SV-502 and SV-503 are UL and CSA approved.

Ordering Example: SV-501, brass valve, 1/2 NPT connection, \$192.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters