


HIGH WATT DENSITY, QUARTZ-FACED INFRARED RADIANT PANEL HEATERS

QC and QH Series



\$270

Basic Unit



- ✓ **High Watt Density**
QC Series: 40 W/in²
QH Series: 60 W/in²
- ✓ **High Temperature 1800°F (981°C)**
- ✓ **High Purity Fused Quartz Glass Emitting Face**
- ✓ **Output Wavelength Between 2.5 and 6 Microns**
- ✓ **Heavy Gauge Aluminized Steel Housing**

CAUTION AND WARNING!

Fire and electrical shock may result if products are used improperly or installed or used by non-qualified personnel. See inside back cover for additional warnings.

APPLICATIONS

- ✓ **Textile Drying**
- ✓ **Glass Processing**
- ✓ **Thermoforming**
- ✓ **Film Shrinking**
- ✓ **Powder Coating**
- ✓ **Paint Finishing**

OMEGALUX® QH and QC Series quartz infrared radiant panel heaters have the most powerful power output of any infrared panel heater available. They use a fused quartz glass face that is grooved to provide coil support. The QC series uses a 98% pure fused quartz and the QH series uses a 99% pure fused quartz face. This allows for watt densities up to 60 W/in² with a maximum temperature rating of 1800°F (981°C). The glass face is cleanable and can withstand great thermal shock.

The housing is made of rugged aluminized steel with the electrical terminal housing on the back.

Mounting studs for easy installation are provided, allowing the heaters to be operated face up or down. An optional 3/16" .476(cm) i.d. quartz thermowell is also available for use with type K thermocouples for temperature control.

The best application for the QC and QH series heaters are where you have little space and need maximum power. They are made in building block sizes from 4" by 10" up to 12" by 12", many in dual voltage models to allow for extra flexibility in installation.

SPECIFICATIONS

Power: 240 Vac, 240/480 Vac dual voltage, 1 phase

Wattage: 1600-8640 watts

Watt Density: QC Series 40 W/in², QH Series 60 W/in²


Maximum Temperature Quartz Face: 1800°F (981°C)

Composition of Emitter Face:

QC series, 98% pure fused quartz;

QH Series, 99% pure fused quartz

Housing: aluminized steel



To Order (Specify Model No.)

Width (in.)	Length (in.)	Wattage	Voltage	Phase	Without Thermowell		With Thermowell		Wgt. (kg)	
					Model No.	Price	Model No.	Price		
40 W/in² QC Series										
4 (10)	10 (25)	1600	240	1	QC-041040	\$270	QC-041040-T	\$300	3 (1.4)	
6 (15)	10 (25)	2400	240/480	1	QC-061040	342	QC-061040-T	373	4 (1.8)	
8 (20)	10 (25)	3200	240/480	1	QC-081040	415	QC-081040-T	445	5.5 (2.5)	
10 (25)	10 (25)	4000	240/480	1	QC-101040	488	QC-101040-T	518	7 (3.2)	
12 (30)	10 (25)	4800	240/480	1	QC-121040	560	QC-121040-T	590	8.3 (3.8)	
6 (15)	12 (30)	2880	240/480	1	QC-061240	385	QC-061240-T	415	5 (2.3)	
12 (30)	12 (30)	5760	240/480	1	QC-121240	648	QC-121240-T	678	10 (4.5)	
60 W/in² QH Series										
4 (10)	10 (25)	2400	240/480	1	QH-041060	323	QH-041060-T	353	3 (1.4)	
6 (15)	10 (25)	3600	240/480	1	QH-061060	415	QH-061060-T	445	4 (1.8)	
8 (20)	10 (25)	4800	240/480	1	QH-081060	508	QH-081060-T	538	5.5 (2.5)	
10 (25)	10 (25)	6000	240/480	1	QH-101060	600	QH-101060-T	630	7 (3.2)	
12 (30)	10 (25)	7200	240/480	1	QH-121060	693	QH-121060-T	723	8.3 (3.8)	
6 (15)	12 (30)	4320	240/480	1	QH-061260	470	QH-061260-T	508	5 (2.3)	
12 (30)	12 (30)	8640	240/480	1	QH-121260	803	QH-121260-T	833	10 (4.5)	

Comes with complete operator's manual, electrical and mounting hardware.

Ordering Example: QC-061040-T is a 40 W/in², 240 watt, dual voltage 240/480 Vac heater with optional thermowell, \$373.

** Thermowell accepts 3/16" diameter probes



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters