



Infrared Thermometer with Circle/Dot Laser Sighting

OSXL450
£39⁵⁰



- ✓ Measurement Range
-20 to 320°C
- ✓ Fixed 0.95 Emissivity
- ✓ 6:1 Field of View
- ✓ Auto Power-Off
- ✓ Backlit Display for
Night Use
- ✓ Laser Circle/Dot Sight
- ✓ °C/°F Selectable

The OSXL450 is an economical, non-contact thermometer that is simple to operate. Its patented laser sighting system defines the target for point and shoot measurement of temperatures from -20 to 320°C. Reads surface temperatures in less than a second. Includes handy wrist strap and batteries.

Specifications

Temperature Range: -20 to 320°C

Accuracy: ±2°C or 2% of reading, whichever is greater

Repeatability: 2% or 3°F

Response Time: 500 msec, 95%

Spectral Response: 7 to 18 µm

Emissivity: 0.95

Laser Power Output: Less than 1 mW

Ambient Operating Range: 0 to 40°C

Relative Humidity: 10 to 95% non-condensing, at up to 30°C

Storage Temp: -20 to 65°C without battery

Dimensions: 160 x 90 x 43 mm

Weight: 150 g

Power: 9V (included)

Battery Life: 12 hr, with laser on

Distance to Spot Ratio: 6:1

PATENTED

Covered by U.S. and International Patents and pending applications.



OSXL450, £39.50, shown smaller than actual size.


Laser Circle to Dot Switchable™

Built-In Laser Sighting



High Intensity



Single Dot



Circle



AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OSXL450	£39.50	Economical IR thermometer with circle/dot laser
CAL-3-IR	90	Traceable calibration certificate with test results

Comes with 9V battery, wrist strap, and operator's manual.

Ordering Example: OSXL450, infrared thermometer, £39.50

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters