




# Self-Adhesive Thermocouples Moulded Silicone Design for Curved and Flat Surfaces

SA-2 Series  
Start at  
**£20**

- ✓ Ultra-Slim Silicone Rubber for Maximum Flexibility
- ✓ Self-Adhesive Foil Backing for Faster Response Time
- ✓ 2 Styles Available for Flat or Curved Surfaces
- ✓ Resistant to a Variety of Chemicals and Oils
- ✓ Temperature Range -30 to 150°C
- ✓ Available in J, K, T and E—Colour Coded for Instant Thermocouple Recognition
- ✓ 7/0.2 mm Stranded Thermocouple Wire
- ✓ Stripped Leads Standard (A Variety of Connector Options Are Available)

These sensors are available in 2 different mounting styles for flat or curved surfaces. The integral thermocouple sensor is bonded onto the inner surface of the self adhesive aluminum foil strip, which is provided for faster response times.



## Specifications

### Dimensions:

**SA2C:** 15 x 50 mm (0.59 x 1.97")

**SA2F:** 35 x 12 mm (1.38 x 0.47")

**Wire:** 7/0.2 mm stranded thermocouple wire, 1 m (40") and 2 m (80") lengths; custom lengths available

**Custom Lengths,  
Insulations, and  
Configurations  
Available**

**MOST POPULAR MODELS HIGHLIGHTED!**

To Order (Specify Model Number)		
Model No.	Price	Description
<b>SA2C-(*)I</b>	<b>£20.00</b>	15 x 50 mm (0.59 x 1.97") curved surface sensor, 1 m (40") lead wire, stripped ends
<b>SA2C-(*)I-2M</b>	<b>22.00</b>	15 x 50 mm (0.59 x 1.97") curved surface sensor, 2 m (80") lead wire, stripped ends
<b>SA2C-(*)I-3M</b>	<b>24.75</b>	15 x 50 mm (0.59 x 1.97") curved surface sensor, 3 m (120") lead wire, stripped ends
<b>SA2C-(*)I-SMPW-CC</b>	<b>23.50</b>	15 x 50 mm (0.59 x 1.97") curved surface sensor, 1 m (40") lead wire, ultimate mini male connector
<b>SA2F-(*)I</b>	<b>20.00</b>	35 x 12 mm (1.38 x 0.47") flat surface sensor, 1 m (40") lead wire, stripped ends
<b>SA2F-(*)I-2M</b>	<b>22.00</b>	35 x 12 mm (1.38 x 0.47") flat surface sensor, 2 m (80") lead wire, stripped ends
<b>SA2F-(*)I-3M</b>	<b>24.75</b>	35 x 12 mm (1.38 x 0.47") flat surface sensor, 3 m (120") lead wire, stripped ends
<b>SA2F-(*)I-SMPW-CC</b>	<b>23.50</b>	35 x 12 mm (1.38 x 0.47") flat surface sensor, 1 m (40") lead wire, ultimate mini male connector

\* Specify J, K, T or E thermocouple type.


For standard size connector, replace "SMPW-CC" in the part number and replace with "OSTW-CC", no additional charge. For additional lead wire, add £2 per metre.

**Ordering Example:** SA2C-KI-2M-SMPW-CC, self-adhesive silicone sensor for curved surfaces, Type K, 2 m (80") lead wire with ultimate mini male cable clamp connector, £23.50 + £2 = **£25.50**.





Termination options are available for easy operation in conjunction with OMEGA handheld thermometers or other instruments:



Miniature Thermocouple Plug  
SMPW-M (Add £3.50)  
(e.g., SA2C-KI-SMPW-M)



Crimped Ferrules  
CF (Add £3.50)  
(e.g., SA2C-KI-CF)



Twisted/Shielded Thermocouple Wire  
(e.g., TT-KI-24S-TWSH-10M, £28)



4 to 20 Milliamp Transmitter  
STCTX (Add £55)  
(e.g., SA2C-KI-STCTX-K1)

Turn these sensors into complete measurement systems with the following popular instrument options:



HH802W  
Handheld thermometer with  
Wireless Data Transmission, £104  
visit [omega.co.uk](http://omega.co.uk)



HH11A  
Handheld Thermometer,  
£43.50  
see page L-6



OM-DAQPRO-5300  
Handheld Datalogger, £665  
see page R-7



iDRX/iDRN  
DIN Rail Mount Signal  
Conditioners with Analogue,  
RS232 or RS485 Output, £161  
see page N-5



iDR  
DIN Rail Mount  
Controller/Transmitter with  
Optional Analogue, Control and  
Ethernet Outputs, from £161  
see page N-13



DP41-B  
6-Digit Panel Meter with High  
Accuracy and Resolution, £399  
see page M-19




DPI32, £101  
see page M-11



UWTC-1  
Wireless Thermocouple  
Transmitter, £84  
see page N-1

**AVAILABLE FROM STOCK IN CONVENIENT 5-PACKS!**

Cable ties available in packs of 5. Order part number SA2C-CT at £4.30/pack of 5.



# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

**www.omega.co.uk**



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters