

Block Calibrators



CL122-1, \$5750, shown smaller than actual size.

CL120/CL134 Series
Starts at
\$2600



- ✓ Capable of Simultaneous Heat and Cool Sourcing in 1 Unit
- ✓ Universal Jaw is Ideal for Accepting Irregularly Shaped Probes and Sensors
- ✓ Portable for Field or Laboratory Use
- ✓ CE Approved
- ✓ NIST-Traceable Certificate of Calibration
- ✓ 115 V Power, 230 V Optional

CL120 Series Calibration COOL/HEAT Source


The CL120 Series is capable of simultaneous heat and cool sourcing in 1 unit and is available with either 1 or 2 modules. You select the combination of modules: COOL source only, HEAT source only, COOL source and HEAT source, or 2 HEAT sources. Both the COOL and HEAT sources are available with the universal jaw or a "five hole block."

A dual module system with simultaneous cooling and heating is a significant advantage, because temperature sensors are rarely tested at only 1 temperature. The most common procedure is to test at 0°C (32°F) and at the maximum temperature, thereby characterizing the offset and gain errors. Two HEAT source systems may also be ordered.

NIST Calibration Traceability Satisfies ISO and FDA Thermal Validation requirements

OMEGA certifies the accuracy of its products by using working standard test equipment that is compared to equipment calibrated yearly at NIST (National Institute of Standards and Technology) and redundant equipment calibrated at an independent lab that maintains standards traceable to NIST. This NIST-traceable documentation is provided for each calibration including the actual calibration data.

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.



CL134-5, \$6450, shown smaller than actual size.

CL134 Series Temperature Source/Measure

The CL134 Series has the same features as the CL120 but includes measurement capabilities. This additional feature simplifies the testing of temperature sensors by conveniently housing both the source and measure in one package. The CL134 Series has 3 distinct capabilities:

1. A COOL source (either universal jaw or "5 hole block") with range down to -30°C (-22°F)
2. A HEAT source with range to 500°C (932°F) with universal jaw or range to 700°C (1292°F) with a "5 hole block;" the CL134 Series may be ordered with 2 HEAT sources and no COOL source
3. Measures thermocouples, RTDs, current and voltage

Input Type		Range	Accuracy*
Process Voltage		0 to 100 mV, 0 to 1V, 0 to 10 Vdc	0.03% rdg
Process Current		0 to 20 mA, 4 to 20 mA	0.03% rdg
J	Iron-Constantan	-346 to 1400°F	0.7°F
K	CHROMEPA®-ALOMEGA®	-454 to -256°F	1.8°F
		-256 to 2502°F	0.7°F
T	Copper-Constantan	-454 to -310°F	1.8°F
		-310 to 752°F	0.7°F
E	CHROMEPA®-Constantan	-454 to -364°F	1.8°F
		-364 to 1832°F	0.7°F
R	Pt/13%Rh-Pt	-58 to 104°F	1.8°F
S	Pt/10%Rh-Pt	104 to 3250°F	0.9°F
		-58 to 212°F	1.8°F
B	30%Rh-Pt/6%Rh-Pt	212 to 1184°F	1.8°F
		1184 to 3308°F	0.9°F
C	5%Re-W/26%Re-W	32 to 4253°F	0.7°F
		-418 to -148°F	1.8°F
N	Nicrosil-Nisil	-148 to 2372°F	0.7°F
		J	DIN
RTD	Pt, 385, 100 Ω	-328 to 1652°F	0.3°F
	Pt, 392, 100 Ω	-328 to 1562°F	0.3°F

* Accuracy (all ±) includes maximum linearization error.

Specifications

Internal Reference Sensor: Pt RTD with repeatability better than 0.05°C after repeated cycling to 700°C

Ramp Mode: Can be set in 0.1°/min increments

Ambient Temperature: 4 to 40°C (39 to 104°F)

Case Dimensions:


CL120: Aluminum, 213 H x 292 W x 178 mm D (8.4 x 11.5 x 7"); removable top 64 mm high (2.5")

CL134: Aluminum, 254 H x 406 W x 229 mm D (10 x 16.0 x 9"); removable top 64 mm (2.5" D)

Power: 90 to 130 Vac, 210 to 250 Vac (specify option 230) 800 VA max, 50/60Hz



The operator controls are the up/down pushbuttons for the setpoint, and ON/OFF for the COOL/HEAT sources. The calibration controls (A, F) are recessed and digitally locked out. The readout units may be set to °C or °F with 0.1° resolution up to 537.0°C (999.9°F). A ramp mode may be accessed to test temperature transmitter trip points.




Universal Jaw

Illustrated is an industrial temperature probe with a ferrule. This probe cannot be tested in a conventional drilled hole because the ferrule prevents good contact between the probe and the metal block. Heat Q1 flows down the stem of the probe, causing the probe output to read less than the calibration temperature as sensed by the internal reference RTD. This effect is referred to as stem loss.

The universal jaw clamps around the probe with actively heated jaws and injects the amount of heat Q2 needed to neutralize the stem loss. For the COOL source, the universal jaw works similarly, except the directions of Q1 and Q2 are reversed.



Universal jaw is ideal for irregularly shaped probes.



5-hole block diameters: 1.6, 3.2, 4.8, 6.4, and 9.5 mm (1/16, 1/8, 3/16, 1/4, and 3/8").



General Specifications	COOL Source Universal Jaw	COOL Source 5 Hole Block	Heat Source Universal Jaw	Heat Source 5 Hole Block
Range °C Range °F	Ambient to -30° Ambient to -22° range is 50°C (90°F) below ambient		30° to 500° 86° to 932°	30° to 700° 86° to 1292°
Accuracy ¹	±0.1°C (±0.2°F) for probes 6.4 mm (0.25") and smaller		±(0.05% of setpoint + 0.1°C [0.2°F]) for probes 6.4 mm (0.25") and smaller	
	±0.2°C (0.4°F) for probes >6.4 to 12.7 mm (0.25 to 0.5")		±(0.1% of setpoint + 0.1°C [0.2°F]) for probes >6.4 to 12.7 mm (0.25 to 0.5")	
Resolution	0.1°C or °F		0.1°C or °F	0.1° to 537°C (999°F) 1° above 537°C (999°F)
Stability ²	±0.05°C (0.1°F)		±0.05°C (0.1°F)	
Repeatability ³	±0.05°C (0.1°F)		±0.05°C (0.1°F)	
Uniformity X-Y Axis (Across Flats)	<±0.03°C (0.05°F)		<±0.03°C (0.05°F)	<0.1°C (0.2°F)
Z Axis (Depth)	<0.1°C (0.2°F) from 102 mm (4") deep to 51 mm (2") deep		<0.1°C (0.2°F) from 4" (102 mm) deep to jaws	<0.1% of setpoint from 102 mm (4") deep to 51 mm (2") deep
Cool/Heat Time	5 minutes to COOL and stabilize from ambient to 0°C (32°F)		10 minutes to HEAT and stabilize @ 300°C	12 minutes to HEAT and stabilize @ 600°C
Metal Block	Aluminum	Aluminum	Aluminum	Bronze Alloy
	Jaw accepts up to 12.7 mm (0.5") drilled holes 3.2, 4.8, 6.4 mm (1/8, 3/16, 1/4") 102 mm (4") deep	Drilled holes 1.6, 3.2, 4.8, 6.4, 9.5 mm (1/16, 1/8, 3/16, 1/4, 3/8") 102 mm (4") deep; other holes available	Jaw accepts up to 12.7 mm (0.5") drilled holes 3.2, 4.8, 6.4 mm (1/8, 3/16, 1/4") 102 mm (4") deep	Drilled holes 1.6, 3.2, 4.8, 6.4, 9.5 mm (1/16, 1/8, 3/16, 1/4, 3/8") 102 mm (4") deep; other holes available

Cooling method: Peltier elements.

¹ Accuracy for 1 year with ambient between 20° to 26°C.

² Measured for 24 hours with ambient between 20° to 26°C.

³ Measured with rosemount 162CE as follows: 1. Measure temperature at 100°C. 2. Heat to maximum (500°C for universal jaw, 700°C for 5 hole block). 3. Remeasure at 100°C. The difference between 1. and 3. is <0.05°C.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
CL121-1	\$3250	Block calibrator with single module COOL universal jaw -30°C (-22°F)
CL121-2	3050	Block calibrator with single module HEAT universal jaw 500°C (932°F)
CL121-3	2800	Block calibrator with single module COOL 5-hole block -30°C (-22°F)
CL121-4	2600	Block calibrator with single module HEAT 5-hole block 700°C (1292°F)
CL122-1	5750	Block calibrator with dual module COOL universal jaw -30°C (-22°F), HEAT universal jaw 500°C (932°F)
CL122-2	5550	Block calibrator with dual module HEAT universal jaw 500°C (932°F)
CL122-4	4850	Block calibrator with dual module COOL 5-hole block -30°C (-22°F), HEAT 5-hole block 700°C (1292°F)
CL122-5	4650	Block calibrator with dual module HEAT 5-hole block 700°C (1292°F)

Note: 2 COOL sources not available in 1 instrument. Add "-230" suffix for 230 Vac power option and add \$75 to price.

Ordering Example: CL121-1, block calibrator with a cooling source using the universal jaw, \$3250.

OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$350) \$3250 + 350 = \$3600.

Model No.	Price	Description
CL134-1	\$7550	Block calibrator with COOL universal jaw -30°C (-22°F), HEAT universal jaw 500°C (932°F), and measurement readout
CL134-2	7350	Block calibrator with dual mode HEAT universal jaw 500°C (932°F), and measurement readout
CL134-4	6650	Block calibrator with COOL 5 hole block -30°C (-22°F) HEAT 5-hole block 700°C (1292°F), and measurement readout
CL134-5	6450	Block calibrator with HEAT 5 hole block 700°C (1292°F), and measurement readout (dual heat sources)

Add "-230" suffix for 230 Vac power option and add \$75 to price.

K, J, T, E, C, S, R, B, and N thermocouple types may be read with 0.1°C or °F resolution. RTDs (resistance temperature detectors) may be tested in 2-, 3-, or 4-wire modes with alpha values of 0.385 or 0.392. The outputs of temperature transmitters may be read directly by the MEASURE unit in either mA or Vdc.

Ordering Example: CL134-4, block calibrator with cooling and heating source using standard 5-hole block, \$6650.

OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$350) \$6650 + 350 = \$7000.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters