



# 1/16 DIN High/Low Limit Controller

Panel Punches Available Visit [omega.com/panelpunches](http://omega.com/panelpunches)

CN3271 Series Starts at **\$220**



CN3271-R1, \$220, shown actual size.

- ✓ High-Limit, Low-Limit or High and Low Limits
- ✓ Peak Temperature Detection
- ✓ Universal Sensor Inputs
- ✓ NEMA 4X (IP65) Splashproof Faceplate
- ✓ Coded Security Levels
- ✓ Alarm Inhibit on Power-Up and Setpoint Change
- ✓ Remote Reset Option

The CN3271 Series high-/low-limit controllers are designed to provide reliable protection of processes, process equipment and personnel. These are UL listed overtemperature (or undertemperature) controllers, and are FM approved as limit controllers. Universal sensor inputs allow the CN3271 Series used in temperature, pressure and other processes. Versatile, easy-to-install and simple to operate, the CN3271 Series provides all of the limit control functions and features of larger and more costly controllers in a space-efficient, 1/16 DIN package. With a NEMA 4X (IP65) rated faceplate, the controller is an excellent choice for washdown environments such as food processing plants.

The CN3271 Series offers sophisticated LED displays of process information such as shutdown duration in hours and minutes, and maximum or minimum process values measured during a shutdown. Temperature input is field programmable for °C or °F. Process input decimal points and range are programmable from -1999 to 9999.

## Specifications

**Accuracy:** ±0.2% FS  
**Output #1 Relay:** SPDT contact, 3 A @ 250 Vac (resistive) limit output, normally energized (latching high, low or high and low)  
**Output #2 Relay:** NO, SPST contact, 2 A @ 250 Vac (resistive) normally energized/normally de-energized, inhibit on power-up and setpoint changes, latching/non-latching (field selectable: process, deviation, band)  
**Digital Input Option:** Dry contact input, for remote acknowledgement; RS485, MODBUS® communications included with “-DI” option  
**Power:** 100 to 240 Vac, 50 to 60 Hz (24 Vac/dc optional) ±10% nominal value; consumption, 8 VA

**Operating Environment:** 0 to 50°C (30 to 122°F) 20 to 85% relative humidity non-condensing  
**Panel Cutout:** 45 mm² (1.77 in²)  
**Dimensions:** 48 mm² (1.9 in²)  
**Depth Behind Panel:** 105 mm (4.33") or 122 mm (4.8") with digital input option  
**Weight:** 250 g (8.75 oz)

Input		
Thermocouple	J	-100 to 1000°C (-150 to 1830°F)
	K	-100 to 1370°C (-150 to 2500°F)
	E	-100 to 800°C (-150 to 1470°F)
	T	-200 to 400°C (-330 to 750°F)
	N	-100 to 1400°C (-150 to 2550°F)
	R/S	-50 to 1760°C (-60 to 3200°F)
	B	0 to 1820°C (32 to 3300°F)
	L (J DIN)	-100 to 900°C (-150 to 1650°F)
	U (T DIN)	-200 to 600°C (-330 to 1110°F)
	PL II	-100 to 1400°C (-150 to 2550°F)
	C/D/G	0 to 2300°C (32 to 4170°F)
RTD, 3-Wire, 100 Ω, α = 0.00385		-200 to 850°C (-330 to 1560°F)
Process (DC)		0 to 20 or 4 to 20 mA, 0 to 60 or 12 to 60 mV, 0 to 5, 1 to 5, 0 to 10, or 2 to 10 Vdc

**MOST POPULAR MODELS HIGHLIGHTED!**

## To Order (Specify Model Number)

Model No.	Price	Description
CN3271-R1	\$220	Limit controller, 1/16 DIN, single relay
CN3271-R1-R2	240	Limit controller, 1/16 DIN, dual relays
CN3271-R1-R2-DI	345	Limit controller, dual relays, digital reset input
CN3271-R1-LV	260	Limit controller, single relay, low voltage power
CN3271-R1-R2-LV	280	Limit controller, dual relays, low voltage power
CN3271-R1-R2-DI-LV	405	Limit controller, dual relays, DI reset, low power
DPP-4	475	1/16 DIN panel punch

Comes complete with operator's manual.  
**Ordering Examples:** CN3271-R1-R2-DI, limit controller with dual relays and digital reset input, \$345.  
 CN3271-R1-LV, limit controller with single relay, low voltage power, \$260.

**Additional Features Include**

- ✓ **Power-Up Programming Options**— Select from powering up in power-down condition, always in alarm, or in the condition at power-up.
- ✓ **Limit Acknowledge**— Can acknowledge, even though you are still in alarm condition (output does not reset until condition cleared), or reset when not in alarm condition.
- ✓ **Alarm Output 2 with “Silence” Option**— Used for horn outputs. Output 2 can be reset before the condition resets.

# omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters