

SUPERMETER™

with Patented Laser Sighting

Non-Contact Temperature Measurement

3 METERS IN 1


HHM290
£164



UNIQUE FEATURES!

- ✓ Built-In Infrared Pyrometer with Switchable Laser Dot/Circle Sighting
- ✓ Adjustable Emissivity with 10:1 Field of View
- ✓ Full-Function Auto-Ranging Digital Multimeter
- ✓ Measures Capacitance, Inductance, and Frequency
- ✓ Dual Thermocouple Input (Non-Isolated) with Differential Temperature Function
- ✓ Powered by 6 "AA" Batteries or DC Adaptor
- ✓ Built-In Tripod Mount
- ✓ Monitors Min, Max, Avg Readings
- ✓ Rugged Housing with Removable Holster

Laser Circle to Dot Switchable™



True RMS
Measurement!

Non-Contact
Temperature
Measurement

Differential
Temperature
Measurement



PATENTED

Covered by U.S. and
International patents and
pending applications

6 "AA" batteries
included.

CAUTION! – This product
is not intended for medical
use or use on humans

**True RMS
Measurement!**

See top view
on page 283

**Shock-Resistant,
Removable Boot**

SUPERMETER™ 3 METERS IN 1!

Includes:

- Test Lead Set
- 2 Type K Beaded Wire Thermocouples with Spool Caps
- 6 "AA" Batteries
- Rubber Boot
- Tilt Stand
- Spare Fuse
- Operator's Manual
- ✓ Built-In Non-Contact Infrared Pyrometer
- ✓ Full-Function Multimeter Featuring Min, Max, and Average Readings
- ✓ Dual Type K Thermocouple Inputs (Non-Isolated) and Selectable Temperature Display (T1 and T2) as well as Differential Temperature (T1-T2)



**Everything
Included!**

Technology Breakthrough!

"It's a technician's dream come true!" OMEGA's new, patented, "all-in-one" The HHM290 SUPERMETER™ combines the functions of a true RMS full-function multimeter, a non-contact infrared pyrometer with laser sighting and a dual-input Type K (non-isolated) thermocouple meter with a differential measurement feature into 1 power-packed handheld instrument. The multimeter measures DC/AC voltage,

current, resistance, frequency, capacitance, and features a built-in logic and diode tester. The infrared pyrometer offers adjustable emissivity, a wide temperature range, a 10:1 field of view, and a laser sighting selector switch. With this switch, the user can select between "a single laser dot" for hot spot locating and "a laser circle pattern" that outlines the optical field of view for average area measurement. The large

backlit LCD shows simultaneous readings in both digital and analogue bar graph format with settings for min/max and average readings. Features include auto power-off, fused multimeter inputs, and battery or AC wall adaptor power. The HHM290 comes with safety test leads, dual Type K temperature probes, rubber protective boot, batteries, spare fuse, and operator's manual.

Specifications

General

Operating Temperature:
0 to 40°C

Power: 6 "AA" batteries
(included) or optional DC adaptor,
9 Vdc @ 200 mA

Display: Dual backlit LCD with digital
readout of 43,000 counts and analogue
bar graph of 40 counts

Display Resolution:

Range	Display Resolution
0 to 4.3	0.0001
0 to 43	0.001
0 to 430	0.01
0 to 4300	0.1
0 to 43000	1

Low Battery Indicator:

Icon on LCD

Battery Life: 100 hours normal usage
without laser or LCD backlight

Tripod Mount: ¼" to 20 UNC

Dimensions: 203 H x 101 W x 51 mm D

Weight: 640 g

Multimeter

DC Voltage

Range: 430 mV to 1000V

Accuracy: 0.25% rdg + 10 digits

AC Voltage

Range: 430 mVac to 750 Vac

Accuracy: 1% rdg + 20 digits

DC Current

Range: 430 µA to 10 A

Accuracy:

0.5% rdg + 10 digits (up to 43 mA)

2% rdg + 10 digits (up to 10 A)

AC Current

Range: 430 µA to 10 A

Accuracy:

1% rdg + 20 digits (up to 430 mA)

2.5% rdg + 20 digits (up to 10 A)

Resistance

Range: Up to 41 M

Accuracy: 0.3% rdg + 20 digits

(Up to 4.3 M)

Frequency

Range: Up to 1 MHz


Accuracy: 0.1% rdg + 3 digits

Capacitance

Range: 4.3 nF to 430 µF

Accuracy: 5% rdg + 100 digits

**Switch
from Circle!**



Differential temperature
sensors included.

**Switch from High
Intensity Dot!**



Temperature Measurement

Thermocouple Type:

Dual Type K (non-isolated)

Display: T1, T2, or T1-T2

Accuracy: 2% rdg or 2°C

Measurement Range: -200 to 1372°C

Infrared Measurement

Measurement Range: -20 to 550°C

Accuracy @ 22°C: 2% rdg
or 1.7°C, whichever is greater

Resolution: 1°C or °F

Optical Field of View: 10:1

Spectral Response:

8 to 14 microns

Emissivity:

0.1 to 1
adjustable

Response Time:

1.5 seconds

Laser Sighting

Wavelength (Colour): 630 to 670 nm (red)

Operating Distance:

Laser Dot: Up to 12 m

Laser Circle: Up to 4.5 m

Maximum Optical Power Output:


<1 mW Class II laser product

Laser Indicator: Laser icon on the display

Tripod mountable.


Shown with
tilt stand and
rubber boot
(included).

Optional AC adaptor
(see "To Order"
on next page).




SUPERMETER™ 3 METERS IN 1!

Immediate
Delivery
Available



Patented Laser Sighting Circle or Dot Switchable




PATENTED

Covered by U.S and International patents and pending applications

- ✓ Built-In Non-Contact Infrared Pyrometer
- ✓ Full-Function Multimeter Featuring Min, Max, and Average Readings
- ✓ Dual Type K Thermocouple Input (Non-Isolated) and Temperature Display (T1 and T2) as well as Differential Temperature (T1-T2)
- ✓ Built-In Patented Laser Circle Sighting for Infrared Measurement
- ✓ Digital Emissivity Adjustment from 0.1 to 1.00 in 0.01 Steps
- ✓ Optical Field of View of 10:1 (Distance to Spot Size)
- ✓ High-Performance, Rugged Design with Large Backlit LCD
- ✓ Measures Voltage, Current, Resistance, Capacitance, Inductance, and Frequency
- ✓ Built-In Diode and Logic Test
- ✓ Battery as well as Optional AC Power
- ✓ Auto Power-Off
- ✓ Tripod Mount and Built-In Rubber Boot

10:1 Field of View



AVAILABLE FOR FAST DELIVERY!


To Order (Specify Model Number)

Model No.	Price	Description
HHM290	£164.00	Digital multimeter/infrared thermometer with laser sighting dot/circle switch
Options and Accessories		
HHM290-SC	£10.00	Soft carrying case
HHM-TL	3.40	Replacement test leads (1 set)
OS520-ADAPTOR-220V	16.75	220 Vac adaptor
KTSS-HH-IEC	19.50	General purpose immersion probe, Type K
88001K-IEC	74.00	General purpose surface probe, Type K
CAL-3-IR [†]	90.00	Traceable calibration certificate
TRIPOD	30.00	Lightweight tripod with soft carrying case

[†] Consult Sales for prices on additional calibration services.

Comes with rubber boot, 2 Type K beaded wire thermocouples, 6 "AA" alkaline batteries, test leads and operator's manual.

Ordering Example: HHM290, Digital multimeter/infrared thermometer with laser sighting, HHM290-SC, soft carrying case, KTSS-HH-IEC, general purpose immersion probe, CAL-3-IR, traceable calibration, and TRIPOD, £164 + 10 + 19.50 + 90 + 30 = **£313.50**.



omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters