


Tubular Thermistor Sensor With Threaded Mounting Fitting



ON-970 and ON-910 Series

\$55



- ✓ Threaded Fitting Provides 1/8" NPT Thread for Installation in Pipes or Closed Vessels
- ✓ Can Be Used in Liquid Immersion and Pressurized Applications
- ✓ Available in 5 Resistance Values To Fit Your Instrumentation Needs
- ✓ Maximum Temperature 100°C (212°F)

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)						
Model Number	Price	Resistance @ 25°C	Interchangeability @ 0 to 70°C	Max Temp	Cable Length	Cable Termination
ON-(**)-44004	\$55	2252 Ω	±0.2°C	100°C (212°F)	300 mm (12")	Stripped
ON-(**)-44005	55	3000 Ω	±0.2°C	100°C (212°F)	300 mm (12")	Stripped
ON-(**)-44007	55	5000 Ω	±0.2°C	100°C (212°F)	300 mm (12")	Stripped
ON-(**)-44006	55	10000 Ω	±0.2°C	100°C (212°F)	300 mm (12")	Stripped
ON-(**)-44008	55	30000 Ω	±0.2°C	100°C (212°F)	300 mm (12")	Stripped

** Insert "ON-970" (5") or "ON-910" (4.5") into model number for desired thermistor length.

Notes: For additional cable length, add required length (in inches) to end of the model number and \$0.80/ft to the price.

Ordering Examples: ON-970-44004-36-PP, fitting mount tubular thermistor sensor with a resistance of 2252 Ω @ 25°C and an interchangeability of ±0.2°C, 900 mm (36") of PFA insulated and jacketed cable with a phone plug connector, \$55 + (2 x \$0.80) + \$7 = \$63.60. ON-910-44034-36-PP, fitting mount tubular thermistor sensor with a resistance of 5000 Ω @ 25°C and an interchangeability of ±0.1°C, 900 mm (36") of PVC insulated and jacketed cable and a phone plug connector, \$55 + \$11 + (2 x \$0.80) + \$7 = \$74.60.

Optional Thermistors

Model Number	Additional Price	Resistance @ 25°C (Ω)	Maximum Working Temp	Interchangeability @ 0 to 70°C	Storage and Working Temp for Best Stability
44033	\$11	2252	75°C (165°F)	±0.1°C	-80 to 75°C (-110 to 165°F)
44030	11	3000	75°C (165°F)	±0.1°C	-80 to 75°C (-110 to 165°F)
44034	11	5000	75°C (165°F)	±0.1°C	-80 to 75°C (-110 to 165°F)
44031	11	10,000	75°C (165°F)	±0.1°C	-80 to 75°C (-110 to 165°F)
44032	11	30,000	75°C (165°F)	±0.1°C	-80 to 75°C (-110 to 165°F)

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters