

Reversible Temperature Indicators

RLC-50 Series Thermometers

(Multi-Temp Liquid Crystal Strips)

- ✓ Self-Adhesive
- ✓ Clear, Easy to Read in °C and °F
- ✓ Used in Heating and Cooling Applications
- ✓ Return to Original State—Can be Used Over and Over
- ✓ Non-Toxic
- ✓ Electrically Non-Conductive

RLC Series labels are ideal for monitoring temperatures of electronic parts, transformers, relays, and motors.

In interpreting liquid crystal labels, please note colour variances.

Specifications

Response Time: Fast—½ to 2 seconds typical

Thickness: Approximately 0.25 mm

Accuracy: ±2°C (3.6°F)

Environment: Avoid prolonged exposure to sunlight and ultraviolet light

Recommended Storage Temperature: 10 to 38°C (50 to 100°F)

GREEN Bar is the actual reading

BROWN Bar is just above the actual reading

BLUE Bar is just below the actual reading

7 Temperature Range Labels

RLC-50-30/0

Temperature:

-30 to 0°C (22 to 32°F)
[5°C (9°F) increments]

Price

pk of 10 pk of 30
£8 £22




RLC-50-0/30

Temperature:

0 to 30°C (32 to 86°F)
[5°C (9°F) increments]

Price

pk of 10 pk of 30
£8 £22



RLC-50-30/60

Temperature:

30 to 60°C (86 to 140°F)
[5°C (9°F) increments]

Price

pk of 10 pk of 30
£8 £22



RLC-50-60/90

Temperature:

60 to 90°C (140 to 194°F)
[5°C (9°F) increments]

Price

pk of 10 pk of 30
£8 £22



RLC-50-30/90

Temperature:

30 to 90°C (86 to 194°F)
[10°C (18°F) increments]

Price

pk of 10 pk of 30
£8 £22



RLC-50-90/120

Temperature:


90 to 120°C (194 to 248°F)
[5°C (9°F) increments]

Price

pk of 10 pk of 30
£8 £22



Models above shown actual size,
12.7 mm W x 44.5 mm L x 0.25 mm T



ALL MODELS IN STOCK FOR FAST OFF-THE-SHELF DELIVERY!

Discount Schedule (Packs)

1-9Net
10-4910%
50-9920%
100-49930%
500+Consult Sales

MOST POPULAR MODELS HIGHLIGHTED!

Temperature Indicators

Model No.	Temperature Range						
RLC-50-30/0(*)	°C -30	-25	-20	-15	-10	-5	0
	°F -22	-13	-4	5	14	23	32
RLC-50-0/30(*)	°C 0	5	10	15	20	25	30
	°F 32	41	50	59	68	77	86
RLC-50-30/60(*)	°C 30	35	40	45	50	55	60
	°F 86	95	104	113	122	131	140
RLC-50-60/90(*)	°C 60	65	70	75	80	85	90
	°F 140	149	158	167	176	185	194
RLC-50-30/90(*)	°C 30	40	50	60	70	80	90
	°F 86	104	122	140	158	176	194
RLC-50-90-120(*)	°C 90	95	100	105	110	115	120
	°F 194	203	212	221	230	239	248

* Insert "-10" for pack of 10 or "-30" for pack of 30.

Ordering Example: RLC-50-90-120-30, 7 temperature range labels [90 to 120°C (194 to 249°F)], pack of 30, £22.





UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters